

556-00252

# HellermannTyton

Article Number: 556-00252

Description: Replacement Power Supply, TT130SMC Printer, Black, 1/EA



Base Data		
	Local Order Number	556-00252
	Type	TT130PWRSLY
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Compact, lightweight design saves space and is easy to transport.</li> <li>• Integrated cutter cuts continuous media to any length.</li> <li>• Designed to work with TagPrint® Pro label design software for ultimate label printing capabilities.</li> </ul>
	Quantity Per	EA
	Product Description	Designed for high-volume industrial-grade printing, HellermannTyton's TT130SMC thermal transfer printer is made of durable materials for long life in a variety of applications and environments. The compact, portable design makes it ideal for transporting to work sites. HellermannTyton thermal transfer printers work flawlessly with HellermannTyton TagPrint® Pro label printing software to create customized labels. An integrated cutter cuts continuous label media and an optional caddy holds larger label stock reels to allow higher capacity printing.
	Technical Description	Replacement Power Supply, TT130SMC Printer, Black
	Short Description	Replacement Power Supply, TT130SMC Printer, Black, 1/EA
Product Dimensions		
	Length L (Imperial)	4.5"
	Length L (Metric)	114.3mm
	Width W (Imperial)	2.25"
	Width W (Metric)	57.15mm
	Height H (Imperial)	1.5"
	Height H (Metric)	38.1mm
	Print Method	Thermal transfer
Material and Specifications		
	Material	Plastic (PL)
	Adhesive Operating Temperature	+40°F to +104°F (+4°C to +40°C)

556-00252



Material and Specifications	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8443913000