

558-00343



Article Number: 558-00343

Description: Adhesive Labels, Solid Color Continuous Roll, 3.0" x 250', VL, Blue, 250 ft/roll



|                    |                               |  |
|--------------------|-------------------------------|--|
| Base Data          |                               |  |
|                    | Local Order Number            | 558-00343  |
|                    | Type                          | HT3BU250   |
|                    | Color                         | Blue (BU)  |
|                    | Features and benefits         | <ul style="list-style-type: none"> <li>• Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.</li> <li>• The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.</li> <li>• Signs can be designed in Tagprint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.</li> </ul> |
|                    | Quantity Per                  | reel   |
|                    | Product Description           | Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.              |
|                    | Technical Description         | Solid Colored Continuous Roll, 3.0" X 250', Vinyl, Blue  |
|                    | Short Description             | Adhesive Labels, Solid Color Continuous Roll, 3.0" x 250', VL, Blue, 250 ft/roll   |
| Product Dimensions |                               |  |
|                    | Length L (Imperial)           | 250.0ft  |
|                    | Length L (Metric)             | 76.20m   |
|                    | Width W (Imperial)            | 3.0"   |
|                    | Width W (Metric)              | 76.2mm   |
|                    | Height H (Imperial)           | 3.0"   |
|                    | Height H (Metric)             | 76.20mm  |
|                    | Print Method                  | Thermal transfer   |
|                    | Vertical Repeat VR (imperial) | 3.0"   |
|                    | Vertical Repeat VR (metric)   | 76.2mm   |
|                    | Width of Liner WL (imperial)  | 3.0"   |

558-00343

**HellermannTyton**

|                             |                                |                                  |
|-----------------------------|--------------------------------|----------------------------------|
| Product Dimensions          | Width of Liner WL (metric)     | 76.2mm                           |
| Material and Specifications |                                |                                  |
|                             | Material                       | Vinyl                            |
|                             | Material Shortcut              | V                                |
|                             | Adhesive                       | Acrylic                          |
|                             | Adhesive Operating Temperature | -40°F to +180°F (-40°C to +82°C) |
|                             | Operating Temperature          | -40°F to +180°F (-40°C to +82°C) |
|                             | ROHS Compliant                 | Yes                              |
| Logistic and Packaging      |                                |                                  |
|                             | Package Quantity (Imperial)    | 250ft                            |
|                             | Package Quantity (Metric)      | 76.2m                            |
|                             | Customs Number(Schedule B)     | 3919102055                       |
|                             | Labels per Column              | 1                                |
|                             | Labels per Row                 | 1                                |