

558-00351



Article Number: 558-00351

Description: Adhesive Labels, Solid Color Continuous Roll, 4.0" x 250', VL, Green, 250 ft/roll



Base Data		
	Local Order Number	558-00351
	Type	HT4GN250
	Color	Green (GN)
	Features and benefits	<ul style="list-style-type: none"> • Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options. • The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment. • Signs can be designed in Tagprint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.
	Quantity Per	reel
	Product Description	Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.
	Technical Description	Solid Colored Continuous Roll, 4.0" X 250', Vinyl, Green
	Short Description	Adhesive Labels, Solid Color Continuous Roll, 4.0" x 250', VL, Green, 250 ft/roll
Product Dimensions		
	Length L (Imperial)	250.0ft
	Length L (Metric)	76.20m
	Width W (Imperial)	4.0"
	Width W (Metric)	101.6mm
	Height H (Imperial)	4.0"
	Height H (Metric)	101.60mm
	Print Method	Thermal transfer
	Vertical Repeat VR (metric)	101.6mm
	Vertical Repeat VR (imperial)	4.0"
	Width of Liner WL (imperial)	4.0"

558-00351

HellermannTyton

Product Dimensions	Width of Liner WL (metric)	101.6mm
Material and Specifications		
	Material	Vinyl
	Material Shortcut	V
	Adhesive	Acrylic
	Adhesive Operating Temperature	-40°F to +180°F (-40°C to +82°C)
	Halogenfree	Yes
	Operating Temperature	-40°F to +180°F (-40°C to +82°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	250ft
	Package Quantity (Metric)	76.2m
	Customs Number(Schedule B)	3919102055
	Labels per Column	1
	Labels per Row	1