

596-00418

HellermannTyton

Article Number: 596-00418



Description: Insert for 596-00189, 596-00190, 596-00191, 1.06" X .59", Plastic, White, 360/pkg



Base Data		
	Local Order Number	596-00418
	Type	WPL15X27
	Color	White (WH)
	Features and benefits	• The legend base inserts are made of high performance polycarbonate. • The inserts can be marked with a standard label or if a plotter is available, can be printed with ink jet or laser etching. • The inserts snap easily into the plastic legend bases for a high contrast and permanent identifier.
	Quantity Per	pack
	Product Description	Plastic Nameplate labels are less costly than plastic or metal engraved plates, saving material costs. Plastic Nameplate labels are made of a UL94VO rated polycarbonate that can be mounted mechanically or using an adhesive backing. HellermannTyton thermal transfer or laser labels can be printed and applied to the inserts and covered with a clear plastic cover to protect printed text.
	Technical Description	Insert for 596-00189, 596-00190, 596-00191, 1.06" X .59", Plastic, White
	Short Description	Insert for 596-00189, 596-00190, 596-00191, 1.06" X .59", Plastic, White, 360/pkg
Product Dimensions		
	Self adhesive (Yes/No)	Yes
	Width W (Imperial)	1.06"
	Width W (Metric)	27mm
	Height H (Imperial)	0.59"
	Height H (Metric)	15mm
	Horizontal Repeat HR (metric)	27mm
	Horizontal Repeat HR (imperial)	1.06"
	Print Method	Thermal transfer
	Vertical Repeat VR (imperial)	0.59"
	Vertical Repeat VR (metric)	15mm

596-00418



Material and Specifications		
	Material	Polycarbonate (PC)
	Material Shortcut	PC
	Flammability	UL 94 V0
	Operating Temperature	-22°F to +266°F (-30°C to +130°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	360
	Package Quantity (Metric)	360
	Customs Number(Schedule B)	3919905060
	Labels per Column	4
	Labels per Row	3