

596-00635

# HellermannTyton

Article Number: 596-00635



Description: Pre-Printed Header Label, CAUTION, 3.0" x 2.0", UV, PET, Yellow, 250/roll

Base Data		
	Local Order Number	596-00635
	Type	3X2CAUTIONUV
	Color	Yellow (YE)
	Features and benefits	<ul style="list-style-type: none"> <li>• Made with UV stable inks and materials for durability and weather resistance.</li> <li>• Supplied with an aggressive adhesive to ensure long life.</li> <li>• Meets NEC &amp; IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.</li> <li>• Pre-printed labels offer significant time and cost savings over high priced plastic engraved phenolic placards and lead time purchased markers.</li> </ul>
	Quantity Per	reel
	Product Description	HellermannTyton Pre-Printed Vinyl Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.
	Technical Description	Pre-Printed Header Label, CAUTION, 3" X 2", UV, Yellow
	Short Description	Pre-Printed Header Label, CAUTION, 3.0" x 2.0", UV, PET, Yellow, 250/roll
Product Dimensions		
	Length L (Imperial)	2.0"
	Length L (Metric)	50.8mm
	Width W (Imperial)	3.0"
	Width W (Metric)	76.2mm
	Height H (Imperial)	2.0"
	Height H (Metric)	50.80mm
	Horizontal Repeat HR (imperial)	3.0"
	Horizontal Repeat HR (metric)	76.2mm
	Width of Liner WL (imperial)	3.2"
	Width of Liner WL (metric)	81.28mm

596-00635



Material and Specifications		
	Material	Type 840/926, Polyester (PET), white (WH) UV stable w/ clear Polyester laminate
	Material Shortcut	840/926
	Halogenfree	Yes
	Operating Temperature	-40°F to +302°F (-40°C to +150°C)
	ROHS Compliant	Yes
	Certification/Specification	UL969
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	250
	Package Quantity (Metric)	250
	Customs Number(Schedule B)	3919102055
	Labels per Column	1
	Labels per Row	1
	Weight (imperial)	3.2oz