

597-00035

HellermannTyton

Article Number: 597-00035

Description: Self-Laminating Tag, Adhesive, Generic Write-On, Blank Lines, 3.0" x .75", Orange, 25/pkg



| | | |
|--------------------|---------------------------------|---|
| Base Data | | |
| | Local Order Number | CTA0753X2 |
| | Type | CTA0753 |
| | Color | White (WH) |
| | Features and benefits | <ul style="list-style-type: none"> • Clear laminating plastic flap permanently protects the writing and data marked on the tag. • Mounting holes for easy mounting using standard cable ties. • Markers can be mounted in any direction, either vertically, horizontally, as a wrap-around identification plate or as a flag for the best visual position on the cable assembly. |
| | Quantity Per | pack |
| | Product Description | <p>HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease.</p> <p>Product Features</p> <ul style="list-style-type: none"> - Easily and conveniently fits in a pants or shirt pocket. - Once loaded, unit allows minimal label exposure to dust and moisture. - Can be used with standard ball point pens or HellermannTyton nylon marking pens. - Excess liner is easily cut-off by tearing it over the edge guide at the front of the unit. - The dispenser can be reloaded over and over again, making it a cost-effective and efficient method of labeling. |
| | Short Description | Self-Laminating Tag, Adhesive, Generic Write-On, Blank Lines, 3.0" x .75", Orange, 25/pkg |
| Product Dimensions | | |
| | Length L (Imperial) | 0.75" |
| | Length L (Metric) | 19.05mm |
| | Width W (Imperial) | 3.0" |
| | Width W (Metric) | 76.2mm |
| | Height H (Imperial) | 1.0" |
| | Height H (Metric) | 25.40mm |
| | Horizontal Repeat HR (imperial) | 1.0" |
| | Horizontal Repeat HR (metric) | 25.40mm |

597-00035



| | | |
|-----------------------------|--------------------------------|-----------------------------------|
| Material and Specifications | | |
| | Material | Polyvinylchloride (PVC) |
| | Material Shortcut | PVC |
| | Adhesive | Acrylic |
| | Adhesive Operating Temperature | -40°F to +302°F (-40°C to +150°C) |
| | Operating Temperature | -40°F to +266°F (-40°C to +130°C) |
| | ROHS Compliant | Yes |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 25 |
| | Package Quantity (Metric) | 25 |
| | Customs Number(Schedule B) | 3919905060 |
| | Labels per Column | 1 |
| | Labels per Row | 1 |
| | Labels per Sheet | 1 |