

852-25063

HellermannTyton



Article Number: 852-25063

Description: Category 6 Modular Keystone Jack Bulk Pack, Ivory, 50/box

Base Data		
	Local Order Number	RJ45FC6B-I
	Type	RJ45FC6
	Color	Ivory (IV)
	Features and benefits	<ul style="list-style-type: none"> • Category 6 jack has been uniquely designed adopting HellermannTyton's globally tried and tested 10-Pin technology which guarantees superior performance and connectivity. • Standard keystone style interface provides flexibility in connecting components. • Unique strain relief design secures cable terminations. • Configured to both TIA 568A and 568B wiring schemes for installation versatility. • Available in 12 colors for easy color coding identification.
	Quantity Per	box
	Product Description	HellermannTyton's GigaBand flush Category 6 modular jack is designed to "future proof" installations. Its patented design uses innovative crosstalk-cancellation technology. The performance of the GigaBand system provides significant margin over TIA Category 6 (ANSI/TIA-568-C.1) and ISO Class E (ISO/IEC-11801, 2nd edition) requirements. The GigaBand system will easily support applications such as Gigabit Ethernet. ETL tested and approved for Category 6 component compliance.
	Technical Description	The performance of the Category 6 system provides significant margin over TIA Category 6 and ISO/IEC 11801 Class D requirements. Adapters are available to enable the keystone jack to be assembled with the GigaBand/Alpha Snap shuttered outlet and 6C angled module.
Product Dimensions	Short Description	Category 6 Modular Keystone Jack Bulk Pack, Ivory, 50/box
	Port count	1
	Width W (Imperial)	13.75"
	Width W (Metric)	19.0mm
	Height H (Imperial)	13.91"
	Height H (Metric)	23.0mm
	Depth D (metric)	42.0mm
	Depth D (imperial)	1.65"

852-25063



Logistic and Packaging		
	Package Quantity (Imperial)	50
	Package Quantity (Metric)	50
	Customs Number(Schedule B)	9030400000
	Weight (Metric)	0.500kg