

854-44334

HellermannTyton



Article Number: 854-44334

Description: Grip Tie, UL94V0-2 Flame Rated, .5" x 12.0", PA6/PP, Maroon, 10/pkg

Base Data		
	Local Order Number	GT.50X12MP2V2
	Type	GT.50X12
	Color	Maroon (MN)
	Features and benefits	<ul style="list-style-type: none"> • UL94V0-2 flame rate material allow use in air handling spaces. • Features quick release for repetitive access to cable and wire. • Can be opened and closed numerous times without failure. • Adjustable so one size can accommodate multiple bundle sizes.
	Quantity Per	bag
	Product Description	The Grip Tie is a low profile, one piece fastening device. Constructed of a hook and loop design, laminated back to back, the Grip Tie features quick release for repetitive access to cable and wire. Grip Ties are available in a variety of colors and are versatile enough for applications ranging from network installations to bundling power cords.
	Short Description	Grip Tie, UL94V0-2 Flame Rated, .5" x 12.0", PA6/PP, Maroon, 10/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	40.0lbs
	Minimum Tensile Strength (Metric)	177.93N
	Length L (Imperial)	12.0"
	Length L (Metric)	304.8mm
	Length L2 (Imperial)	1.5"
	Length L2 (Metric)	38.1mm
	Width W (Imperial)	0.5"
	Width W (Metric)	12.7mm
	Width W2 (Imperial)	1.0"
	Width W2 (Metric)	25.4mm
	Bundle Diameter Max. (Imperial)	3.18"
	Bundle Diameter Max. (Metric)	80.772mm

854-44334



Material and Specifications		
	Material	Polyamide 6 (PA6)
	Material Shortcut	PP
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10
	Customs Number(Schedule B)	9606100000