

855-24200

HellermannTyton

Article Number: 855-24200



Description: Fiber Adapter Panel Preloaded with 8 Duplex LC MM, Beige, 1/pkg

Base Data

Local Order Number	FAP8DMMLC
Type	FAP8DMMLC
Color	Beige (BGE)
Features and benefits	<ul style="list-style-type: none"> • High performance zirconia ceramic ferrules allow for frequent, repeated insertion. • Standard LC, SC, ST, MTP and MTRJ connector options to suit specific applications. • “Snap lock” fixtures for easy and secure mounting. • Meet ANSI/TIA/EIA 568-B standards. • Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements. • GSA compliant panels meet TAA requirements for use in government projects.
Product Description	For customized wall mount and rack mount fiber optic enclosures, HellermannTyton offers panel options featuring a variety of adapters to suit different preferences and applications. In addition to adapter panels with standard LC, SC, ST, MTP and MTRJ connections, HellermannTyton also offers custom solutions. Our adapter panels include options to accommodate OS1/2 in both standard and angled versions, as well as 62.5/125µm OM1, 50/125µm OM2 and 50/125µm 10 Gb OM3/4. HellermannTyton adapter panels are made with zirconia ceramic or phosphor bronze ferrules for minimal insertion loss contribution. Zirconia ceramic ferrules provided excellent durability and are an ideal choice for use in laser optimized multimode and single mode applications. HellermannTyton offers both standard and GSA compliant adapter panels. GSA compliant panels meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government projects.
Technical Description	Adapter Panel Preloaded with 8 Duplex LC MM, Beige
Short Description	Fiber Adapter Panel Preloaded with 8 Duplex LC MM, Beige, 1/pkg

Product Dimensions

Length L (Imperial)	5.09"
Length L (Metric)	129.3mm
Port count	16
Width W (Imperial)	1.14"
Width W (Metric)	28.96mm
Height H (Imperial)	1.14"
Height H (Metric)	29.0mm

855-24200



Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8538907080