

859-30064

Article Number: 859-30064



Description: RNS Series Angled Modular Panel, 2U, Black, 1/ctn

Base Data		
	Local Order Number	RNSAPP2U
	Type	RNA6UXX-PE2USC
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • 2U RNS Series angled modular panel accepts 8 RNS Series short body cassettes and provides copper and fiber solutions in the same footprint. • Simple, easy insertion with push down clip. • Angled design provides increases rack capacity.
	Quantity Per	box
	Product Description	RapidNet is HellermannTyton's patented pre-terminated "connect and go" system which offers a high performance in copper and fiber solutions for data centers and storage area network applications. These pre-terminated solutions do not require on-site termination or certification testing which dramatically reduces installation time up to 85%.
	Technical Description	<p>The RapidNet Angled panel is manufactured from 1.6mm powder coated mild steel making it rigid and robust.</p> <p>The panel has a matt black finish and is screen printed with port numbers 1 to 48 as well as clear port identification labelling areas for easy user identification which can be customised through Alpha Label software at www.htdata.co.uk.</p> <p>The panels is supplied with Screw fixings as standard, panels can also be supplied with Rack Snaps, Cage Nuts or without fixings if required</p>
	Short Description	RNS Series Angled Modular Panel, 2U, Black, 1/ctn
Product Dimensions		
	Port count	48
	Width W (Imperial)	19.0"
	Width W (Metric)	483.0mm
	Height H (Imperial)	3.6"
	Height H (Metric)	88.0mm
	Depth D (imperial)	4.2"
	Depth D (metric)	106.0mm

859-30064



Logistic and Packaging		
	Package Quantity (Imperial)	1