

904-00569

# HellermannTyton

Article Number: 904-00569



Description: FT LC - MT Duplex OM1 Fiber Assembly, 4M, Orange, 1/pkg

Base Data		
	Local Order Number	VFA4LCMTOM1
	Type	VFA4LCMTOM1
	Color	Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> <li>• Pre-radiused zirconia ceramic ferrules for precision alignment.</li> <li>• Industry standard LC, SC, ST or MTRJ connectors to suit specific applications.</li> <li>• Available in 1-5 meter lengths.</li> <li>• 3mm cordage.</li> <li>• Color coded for easy identification.</li> <li>• Individually quality tested for insertion and return loss.</li> <li>• Meet ANSI/TIA/EIA 568-B standards.</li> <li>• Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.</li> </ul>
	Product Description	For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types – standard and GSA compliant. Our standard jumpers combine quality with value, meeting all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, GSA compliant jumpers meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government contract projects.
	Technical Description	FT LC - MT Duplex OM1 Fiber Assembly, 4M, Orange
	Short Description	FT LC - MT Duplex OM1 Fiber Assembly, 4M, Orange, 1/pkg
Product Dimensions		
	Length L (Imperial)	13.1ft
	Length L (Metric)	4.0m
Logistic and Packaging		
	Package Quantity (Imperial)	4
	Package Quantity (Metric)	1

