

904-00778

Article Number: 904-00778



Description: RapidNet Fiber Adapter Panel 6 DUP, MM, SC Beige 1/pkg

Base Data		
	Local Order Number	RNGFAP6DMMSC
	Type	RNGFAP
	Color	Beige (BGE)
	Features and benefits	<ul style="list-style-type: none"> • Ideal for installations with limited access or restricted space. • Available in in 6 or 12 hole configuration. • Allows ruggedized fan-outs to be presented in RapidNet Panels. • Fits into a standard RapidNet Panel. • Supports a maximum of 1152 fibers in 1U of space.
	Product Description	The RapidNet Fiber Adapter Panel is designed to allow the RapidNet solution to be used in areas with limited access or restricted space, where a RapidNet Cassette cannot be used. Panels are pre-loaded with adapters, which allow ruggedized fan-outs to be presented in RapidNet panels - offering a maximum of 288 fibers in a single adapter, or 1152 fibers in 1U of space.
	Technical Description	RapidNet Fiber Adapter Panel 6 DUP, MM, SC Beige
	Short Description	RapidNet Fiber Adapter Panel 6 DUP, MM, SC Beige 1/pkg
Product Dimensions		
	Length L (Imperial)	2.1"
	Length L (Metric)	53.75mm
	Ferrule Type	Phosphor Bronze (PB)
	Fiber Count	12
	Width W (Imperial)	4.0"
	Width W (Metric)	102.7mm
	Height H (Imperial)	1.10"
	Height H (Metric)	27.80mm
Material and Specifications		
	Material	Plastic (PL)
	Material Shortcut	PL

904-00778



Logistic and Packaging		
	Package Quantity (Imperial)	1
	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8538907080
	Weight (Metric)	113.4g
	Weight (imperial)	4oz