

904-00859

HellermannTyton

Article Number: 904-00859

Description: FT LC-LC Duplex OM2 Fiber Assembly, 9M, Orange, 1/pkg



Base Data		
	Local Order Number	VFA9LCLCOM2
	Color	Orange (OG)
	Features and benefits	<ul style="list-style-type: none"> • Pre-radiused zirconia ceramic ferrules for precision alignment. • Industry standard ST, SC, MTRJ or LC connectors to suit specific applications. • Available in 1–5 meter lengths for a variety of applications. • Color coded for easy identification. • Individually quality tested for insertion and return loss. • Meet ANSI/TIA/EIA 568-B standards. • Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.
	Quantity Per	box
	Product Description	For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types—standard and high performance. Our standard jumpers combine quality with value. They meet all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, HellermannTyton high performance jumpers have additional features designed for high performance applications. Our high performance jumpers meet Trade Agreement Act (TAA) requirements, making them suitable for use in General Services Administration (GSA) government contract projects.
	Technical Description	FT LC - LC Duplex OM2 Fiber Assembly, 9M, Orange
	Short Description	FT LC-LC Duplex OM2 Fiber Assembly, 9M, Orange, 1/pkg
Product Dimensions		
	Length L (Imperial)	29.6ft
	Length L (Metric)	9.0m
Material and Specifications		
	Material	Glass Fiber (GF)
	Material Shortcut	GF
Logistic and Packaging		
	Package Quantity (Imperial)	1

904-00859



Logistic and Packaging	Package Quantity (Metric)	1
	Customs Number(Schedule B)	8544700000
	Weight (imperial)	2.7lbs
	Weight (Metric)	861.0g