

904-00930

**HellermannTyton**

Article Number: 904-00930



Description: RapidNet CAT 6 UTP RNC Cassette to Plug, Riser Cable, Blue, 6 port, 1/ctn

|                        |                             |   |
|------------------------|-----------------------------|---|
| Base Data              |                             |   |
|                        | Local Order Number          | RNC6ARBCKTZXXX  |
|                        | Type                        | RapidNet  |
|                        | Color                       | Blue (BU)   |
|                        | Features and benefits       | <ul style="list-style-type: none"><li>• Versatile product offering allows customization for structured cabling requirements.</li><li>• Factory terminated and 100% tested for consistent performance.</li><li>• Short body cassette available for areas with limited space or restricted access.</li><li>• Quick-release lever allows easy insertion and release of the cassette.</li><li>• Patented cassette design allows copper and fiber solutions within the same footprint.</li></ul> |
|                        | Quantity Per                | carton  |
|                        | Product Description         | RapidNet is HellermannTyton's patented pre-terminated "connect and go" system which offers a high performance in copper and fiber solutions for data centers and storage area network applications. These pre-terminated solutions do not require on-site termination or certification testing which dramatically reduces installation time up to 85%.  |
|                        | Technical Description       | <ul style="list-style-type: none"><li>• Jacks are available in a choice of colors to help define network features such as routes, services, hierarchies or security levels.</li></ul>   |
|                        | Short Description           | RapidNet CAT 6 UTP RNC Cassette to Plug, Riser Cable, Blue, 6 port, 1/ctn   |
| Logistic and Packaging |                             |   |
|                        | Package Quantity (Imperial) | 1   |

