


Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	11	See ECN 013096	A.A.C.	04/15/15	K.A.C.	04/15/15



PRODUCT CODE DESCRIPTION

T50R_HS

COLOR

(CONSULT FACTORY FOR AVAILABLE COLORS)



Aerospace Spec Tie SAE AS33671-1 Type 1, Class 1	Type	Cable Range (mm)	Material	A	B	D	E	G	H	Min Loop Tensile Strength (newtons)
no	T50R	3.3 to 50	PA12	1.2 ±0.2	4.6±0.2	5.9 ±0.6	7.6 ±0.9	202.0 ±6.0	7.3 ±0.7	200
no		5.1 to 50	POM							
yes	T50R	1.5 to 50	PA66	1.2 ±0.2	4.6±0.2	5.9 ±0.6	7.6 ±0.9	202.0 ±6.0	7.3 ±0.7	225
no			PA66HS							
yes			PA66UV							
no			PA46							
no			PA66HIRUV							
no			PA66HIRHSUV							
no			PA66VO							
		3 to 50								

SEE CHART

Material


Dimension tolerances unless otherwise specified

.XXXX =
.XXX =
.XX =
.X = NOTED
∠ =

Dimension Units mm

PERFORMANCE SPECIFICATION

ACAD MECH
2014



Drawn

J. STOLZ

2/14/96

Scale

2:1

Computer File Number
CT\CST\2050007_11

Approved

K.A.C.

04/15/15

Title

T50R
STANDARD CABLE TIE

Drawing—No

CT2050007CST

Format

AH

Sheet 1 of 1

ALL PROPRIETARY RIGHTS IN THE
SUBJECT MATTER SHOWN ON THIS
DRAWING ARE EXCLUSIVE
PROPERTY OF HELLERMANN TYTON

HellermannTyton®

7930 N. Faulkner Rd.
Milwaukee, WI 53224
Ph: (414) 355-1130
Fx: (414) 362-8338