


Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	01					
		See ECN 003789	A.A.C.	04/17/03	K.A.C..	04/22/03



Group Unique Numbers	Product Code	Cable Range (mm)	Material	A	B	D	E	G	H	J	K	Min Loop Tensile Strength (newtons)
-	IT50RD_	10 to 44	PA66	1.2 ±0.2	4.7±0.2	6.0 ±0.5	8.0 ±0.5	205.0 ±5.0	6.0 ±0.5	29.0 ±0.5	26.3 ±0.5	225
-	IT50RD_UV		PA66UV									
-	IT50RD_VO		PA66VO									

SEE CHART

Material

Dimension tolerances unless otherwise specified
 .XXXX =
 .XXX =
 .XX =
 .X = NOTED
 < =

Dimension Units mm

PERFORMANCE SPECIFICATION

ACAD 2004

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

Drawn

G. GIEGER

10/10/91

Approved

K.A.C.

04/22/03

HellermannTyton®

7930 N. Faulkner Rd.
 Milwaukee, WI 53224
 Ph: (414) 355-1130
 Fx: (414) 362-8338

Scale

3:1

Computer File Number

CT\CST\2050016_01

Title

IT50RD IDENTIFICATION TIE

Drawing-No

CT2050016CST

Format

AH

Sheet

1 of 1