





name	date	city, state

NOTES



PART NUMBER DESCRIPTION

PBM
 — COLOR (CONTACT FACTORY FOR AVAIL. COLORS)

CABLE TIE SERIES	MAX. PANEL THICKNESS	MOUNTING HOLE DIA.
T18 thru T50	11 GA (.120)	.250

REVISION	level	01
	by	AAM
	date	10/20/00
	ECN #	002199
	part level	A

TOLERANCES	.xxxx = ±.0005/[±.013]
	.xxx = ±.005/[±.13]
	.xx = ±.01/[±.3]
	.x = ±.03/[±.8]
	∠ = ±0.5°
unless otherwise specified	
units	inches / [mm]

PART	number	PBM	phase	PRODUCTION
	name			
	PBM PUSH BUTTON MOUNT			
	material			
	NYLON 6/6			

DRAWING	format	version M	AV	CAD	SW	scale	5:1
	computer file number				previous number		
	MT2008001CST_01						
	drawn	A.A.M.		checked	approved		
	when	10/20/00		date	date		
	type				sheet 1 of 1		
G	number			MT2008001CST			