


Revision level		Revision Record	Changed	Date	Approved	Date
Part	Drawing					
	02	See ECN 012578	AAC	02/06/14	KAC	02/06/14



02		02	02	
TYPE	MATERIAL	COLOR	CABLE RANGE(mm)	MIN LOOP TENSILE STRENGTH (newtons)
T50SOSSB5-HIGH-E-C-CC	PA66HS	GRAY	1 - 35	225
	PA66HS	BLACK		

SEE CHART	
Material	
Dimension tolerances unless otherwise specified	
.xxxx = ±.013 .xxx = ±.13 .xx = ±.3 .x = ±.8 ∠ = ±0.5°	
Dimension Units	millimeters
PERFORMANCE SPECIFICATION	

SW2011	 	Drawn	AAC	10/04/2010	Scale	1:1	Computer File Number	CT10-0532-002CST_02	
		Approved	KAC	02/06/14	Title				T50SOSSB5-HIGH-E-C-CC OUTSIDE SERRATED CABLE TIE WITH OVAL STUD MOUNT
ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNTYTON		HellermannTyton® <i>Cable Management Products</i>			Drawing-No				Format
									AH
		7930 N. Faulkner Rd. Milwaukee, WI 53224 Ph: (414) 355-1130 Fx: (414) 362-8342			CT10-0532-002CST				Sheet 1 of 1