



PART NUMBER DESCRIPTION
CTP14 STD
COLOR

DESCRIPTION	PACKAGE QUANTITY (SEE NOTE 1)	A		B		C
		MIN	MAX	MIN	MAX	
1/4" I.D. IN STANDARD CARTON	3,200					
1/4" I.D. IN BULK CARTON	25,000	.256	.276	.373	.398	.004
3/8" I.D. IN STANDARD CARTON	1,900					
3/8" I.D. IN BULK CARTON	15,000	.341	.380	.497	.526	.005
1/2" I.D. IN STANDARD CARTON	1,100					
1/2" I.D. IN BULK CARTON	8,500	.473	.516	.664	.700	.005
5/8" I.D. IN STANDARD CARTON	800					
5/8" I.D. IN BULK CARTON	5,500	.603	.639	.805	.837	.005
3/4" I.D. IN STANDARD CARTON	550					
3/4" I.D. IN BULK CARTON	4,200	.707	.759	.950	.989	.005
1" I.D. IN STANDARD CARTON	300					
1" I.D. IN BULK CARTON	2,250	1.006	1.055	1.267	1.320	.006
1-1/4" I.D. IN STANDARD CARTON	250					
1-1/4" I.D. IN BULK CARTON	1,800	1.199	1.257	1.446	1.500	.006
1-1/2" I.D. IN STANDARD CARTON	150					
1-1/2" I.D. IN BULK CARTON	1,000	1.566	1.647	1.867	1.947	.006
2" I.D. IN STANDARD CARTON	100					
2" I.D. IN BULK CARTON	800	1.969	2.038	2.285	2.388	.011

REDUCED
NO SCALE

IN
VEN
T
O
R
S

HellermannTyton.

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON.

name	date	city, state

NOTES

- 1) CUT LENGTH TOLERANCE IS $\pm 2.5\%$ OF THE "PACKAGE QUANTITY" LENGTH SHOWN ON CHART.
"PACKAGE QUANTITY" VALUE IS IN FEET.

REVISION	level	03
AW	date	06/15/04
IN	by	AAC
ION	ECN #	004560
	part level	-

TO DIMENSIONS	XXXX=
	.XXX= NOTED
	.XX=
	.X=
	.L=
	unless otherwise specified
	units inches

number	SEE CHART	phase	PRODUCTION
name	CONVULATED TUBING (POLYETHYLENE)		
material	POLYETHYLENE		

DR	contact: 8 mm 8	ACAD	acids NONE
AW	computer file number	DT\SER\3035000_03	previous number
IN	A.A.C.	KAC	
ION	1/17/97	06/17/04	approved
	SERIES	sheet	1 of 1
	number	DT3035000SER	