

SW2010	Revision level		Revision Record	Changed	Date	Approved	Date
	Drawing	Part					
	01	-					

NOMINAL SIZE	TYPE	OD	ID	EXPANSION RANGE (FOR REF ONLY)		L (FT)
				MINIMUM	MAXIMUM	
1/8	BSPSC18	.165	.125	.125	.25	-
1/4	BSPSC14	.29	.25	.1563	.4375	100
1/2	BSPSC12	.54	.50	.25	.75	100
3/4	BSPSC34	.79	.75	.625	1.00	75
1	BSPSC10	1.04	1.00	.75	1.1875	50
1-1/4	BSPSC112	1.29	1.25	1.00	1.50	50
1-1/2	BSPSC112	1.54	1.50	1.25	2.00	50

Material PET	The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied, or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton.	Drawn	AAC	04/12/2011	Article/Type-No	SEE CHART	Scale	1:1	
		Approved	AAC	05/16/2011	Title	PET FRAY RESISTANT EXPANDABLE BRAIDED SLEEVING	Project Number	PRP11-0337	
Units inches		North America Email: corp@htamericas.com Web: www.hellermann.tyton.com				Drawing-No	Production : Phase	Format	AH
Dimension without tolerances details to: .xxxx = ±.0005 .xxx = ±.005 .xx = ±.01 .x = ±.03 None = ±.06 ∠ = ±0.5°						11-0337-003-CSU		Sheet	1/1