


SW2010



Revision level

Drawing

Part

00

-

Revision Record

SEE ECN# 011861

Changed

Date

Approved




Date

AAC

02/02/2012

KAC

02/07/2012

Material
PET

NOMINAL SIZE	TYPE	(OD)	(W) HOOK AND LOOP	(T)	L (FT)
1/2	BSHKLP12	.50	.25	.025	100
3/4	BSHKLP34	.750	.625	.025	100
1 1/4	BSHKLP114	1.25	.625	.025	100
2	BSHKLP20	2.00	.625	.025	100
2 1/2	BSHKLP212	2.50	.625	.025	100

Units inches

Dimension without tolerances
details to:

.xxxx = ±.0005
 .xxx = ±.005
 .xx = ±.01
 .x = ±.03
 None = ±.06
 ∠ = ±0.5°

The copyright of this drawing is
 reserved by HellermannTyton.
 It is issued on condition that it is not
 reproduced, copied, or disclosed to a
 third party, either wholly or in part,
 without the consent of
 HellermannTyton.

Drawn

AAC

02/02/2012

Approved

KAC

02/07/2012

HellermannTyton
 North America
 Email: corp@htamericas.com
 Web: www.hellermann.tyton.com

Article/Type-No

Title
 PET SPLIT BRAIDED SLEEVING WITH
 HOOK AND LOOP

Drawing-No

11-0337-009-CSU

Production : Phase

Scale 1:1

Project Number
 PRP11-0337

Format AH

Sheet 1/1