





AS MOLDED
FULL SIZE

REDUCED
NO SCALE

INVENTORS

HellermannTyton.

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state

NOTES

NOTE:
* 1. INSIDE DIAMETERS ARE MEASURED IN THREE PLACES
SPACED 120° APART EXCLUDING .012 WIDE RIB

* CLAMP RANGE

POSITION	EFFECTIVE TOOTH ENGAGEMENT	DIAMETER
MINIMUM	- 8 -	.571 [14.50]
NOMINAL	- 5 -	.613 [15.57]
MAXIMUM	- 2 -	.654 [16.61]

CHANGE IN DIA./TOOTH = .0138 [351]

REVISION

level	date	by	ECN #
1	08/15/00	AAM	002069
part level	-	-	-

DIMENSIONS

.XXXX=	.XXX= NOTED
.XX=	.X=
∠=	unless otherwise specified
units	inches

PART

number	SNR10GHS	phase	PRODUCTION
name	SNAPPER 10 HOSE CLAMP		
material	NYLON 6/6 13% GLASS FILLED HEAT STABILIZED BLACK		

DRAWING

FORM C	unit 1	QID	ACAD	scale	4X
computer file number	CP\CST\2010001B	previous number	CP\CST\2010001A		
date	K.A.C. 02/27/92	M.E.F. 08/17/00			
type	CUSTOMER	sheet	1 of 1		
number	CP2010001CST				