








AS MOLDED



AS MOLDED
FULL SIZE

HellermannTyton

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON
THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state

NOTES

NOTE:

1. INSIDE DIAMETERS ARE MEASURED IN THREE PLACES SPACED 120°
APART EXCLUDING .015 RIB.
2. 44 TOTAL TEETH, 22 TEETH POSITIONS.

REVISION	DATE	BY	ECN #	PART LEVEL
level 01	11/24/08	AAC	011186	-

DIMENSIONS	UNITS
.XXXX=	unless otherwise specified
.XXX= NOTED	units inches
.XX=	
.X=	
∠=	

number	phase	PRODUCTION
SNP3310		
name	SNAPPER 33 HOSE CLAMP	
material	ACETAL WHITE	

DRAWING	FORMAT C version P		CAD	ACAD	scale	2X
	computer file number			previous number		
	CP\EST\2033001_01					
	drawn	A.A.C.	checked	K.A.C.	approved	
		11/24/08		11/24/08		
	type			CUSTOMER		sheet 1 of 1
	number			CP2033002CST		