





AS MOLDED
FULL SCALE

REDUCED
NO SCALE

HellermannTyton ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON		
name	date	city, state

NOTES

* 1. INSIDE DIAMETERS ARE MEASURED IN THREE PLACES SPACED 120° APART EXCLUDING .015 WIDE RIB

REVISION	level	01
date	04/03/07	
by	AAC	
ECN #	010690	
part level	-	

DIMENSIONS .XXX= NOTED .XX= NOTED .X= NOTED L= NOTED unless otherwise specified units inches/[mm]

number	SNP34-10	phase	PRODUCTION
name	SNAPPER 34 HOSE CLAMP		
material	ACETAL WHITE		

FORMAT C version P	CAD	ACAD	scale	2X
computer file number	CP\2034002_01			
previous number				
drawn	AAC	KAC	checked	approved
date	04/03/07	04/03/07		
type	CUSTOMER		sheet	1 of 1
number	CP2034002CST			