






AS MOLDED
FULL SCALE

PRODUCT CODE DESCRIPTION

SNP12AGHS_ COLOR
(CONSULT FACTORY FOR AVAILABLE COLORS)

INVENTORS	HellermannTyton®			NOTES	1) INSIDE DIAMETERS ARE MEASURED IN THREE PLACES SPACED 120 DEGREES APART EXCLUDING RIB. 2) 12 TOTAL TEETH, 8 TEETH POSITIONS.	REVISION level 04 by AAC date 05/09/2006 ECN # 010418 part level A	DIMENSIONS .XXXX = ±.0005 .XXX = ±.005 .XX = ±.01 .X = ±.03 ∠ = ±0.5° unless otherwise specified units inches	PART number SNP12AGHS_ name SNP12A HOSE CLAMP material NYLON 6/6 13% GLASS FILLED; HEAT STABILIZED	DRAWING formal version N C CAD SW 2006 scale 5:1 computer file name CP05-048-001CST_04 previous drawing number drawn K.A.C. checked K.A.C. approved date 07/28/2004 checked 05/09/2006 approved type Customer sheet 1 of 1 number CP05-048-001CST
	ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON name date city, state								