

HellermannTyton®



ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

0000-123456789

name	date	city, state

NOTES

* POLYPROPYLENE AVAILABLE BASED UPON MINIMUM VOLUME REQUIREMENTS. CONSULT FACTORY



PRODUCT CODE DESCRIPTION

T3D0312

COLOR

(CONSULT FACTORY FOR AVAILABLE COLORS)

PART NUMBER	D REF	W ±.010	H ±.015	E ±.015
T3D0125_	.125	.375	.203	.329
T3D0187_	.1875	.375	.203	.430
T3D0312_	.3125	.375	.203	.495
T3D0375_	.375	.375	.203	.595
T3D0437_	.4375	.375	.203	.574
T3D0500_	.500	.375	.203	.605
T3D0562_	.5625	.375	.203	.606
T3D0625_	.625	.375	.203	.678

REVISION
D level 01
W date 01/11/01
N by AAM
G ECN # 002339
part level A

DIMENSIONS
TOLERANCES
.XXXX=
.XXX= NOTED
.XX=
.X=
L=
unless otherwise specified
units inches

PART
number SEE CHART
name T3D SERIES
T CLAMPS
material * NYLON 6/6
phase PRODUCTION

DRAWING
FORMAT AV version L CAD ACAD scale 2X
computer file number CL\SER\2010300_01
previous number
drawn A.A.M. checked K.A.C. approved
01/11/01 01/15/01
type SERIES sheet 1 of 1
number CL2010300SER