


PART NUMBER DESCRIPTION

GT.375X6
GRIP TIE COLOR

NOTES:

1. AVG SHEAR STRENGTH = 23 PSI
2. AVG PEEL STRENGTH = .5 LBS/IN WIDTH
3. TENSILE LOOP & MAX BUNDLE DIA ARE BASED ON 2" MIN HOOK & LOOP ENGAGEMENT

MIN LOOP TENSILE (LBS)	MAX BUNDLE DIA
40	1.00

I
N
V
E
N
T
O
R
S

HellermannTyton

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNTYTON

name	date	city, state

REV	DATE	BY	ECN #	PART LEVEL
01	04/26/11	AAC	011826	-

DIMENSIONS	TOLERANCES
.XXX=	NOTED
.XX=	
.X=	
∠=	
unless otherwise specified	
units	inches

P
A
R
T

number	phase
GT.375X6	PRODUCTION
name	GT.375 GRIP TIES
material	HOOK & LOOP

DRAWING	FORMAT AH version L			CAD	ACAD	scale 1X	
	computer file number				previous number		
	CT\CST\2007001_01						
	drawn	A.A.C.	checked	K.A.C.	approved		
		04/26/11		04/26/11			
	type	CUSTOMER				sheet	1 of 1
	number CT2007001CST						