




MIN LOOP TENSILE (LBS)	MAX BUNDLE DIA	LENGTH	CATALOG NUMBER
TBD	3.88	15.00	GT .75X15

DESIGN TEAM		INVENTOR(S) / DATE	
HellermannTyton			
ALL PROPRIETARY RIGHTS IN THIS SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNTYTON			
B	DWG REV	DASH - REV	CHANGED RELEASED
	PART NO.	DATE	BY

- NOTES:
1. AVG SHEAR STRENGTH = 23 PSI
 2. AVG PEEL STRENGTH = .5 LBS/IN WIDTH
 3. TENSILE LOOP & MAX BUNDLE DIA ARE BASED ON 2" MIN HOOK & LOOP ENGAGEMENT

DIMENSIONS	VERIFIED	UNITS	TOLERANCES unless otherwise specified	
		☒ in	.XXX= NOTED	.X=
	name	☐ mm	.XX=	<=
	date	☐ mm in		
MATERIAL	HOOK & LOOP			
	AVAILABLE COLORS: BLUE, ORANGE, YELLOW, RED, GREEN, BLACK			
	or engineering approved equivalent			

NAME		PART NAME	
DATE		GT .75X15 GRIP TIE	
drawn	K.A.C.	plot date	6/7/96
checked	6/7/96	scale	FULL
approved		FORMAT AH	VERSION E
		DRAWING NO.	WAS
		drive S	sheet 1 of 1
		CUSTOMER DRAWING NUMBER	
		CT\CST\2007075B	