

SW2014



| Revision level |                |      | Revision Record | Changed | Date      | Approved | Date      |
|----------------|----------------|------|-----------------|---------|-----------|----------|-----------|
| Drawing        | State          | Part |                 |         |           |          |           |
| 00.0           | Design Release |      | SEE ECN# 013484 | GRW     | 6/30/2016 | KAC      | 6/30/2016 |


## FEATURES AND BENEFITS:

- INDUSTRY STANDARD SIZE: LGX FOOTPRINT 5 3/32 [130] X 1 5/32 [29].
- SILKSCREENED PORTS NUMBERS ON BOTH SIDES.
- WIDE VARIETY OF ADAPTER QUANTITY & TYPE.
- MANUFACTURED WITH HIGH PERFORMANCE COMPONENT MATERIALS.
- LOW INSERTION LOSS.
- PRECISE ALIGNMENT FOR GLASS-TO-GLASS CONTACT.
- BLANK ADAPTER STRIP ALSO AVAILABLE TO COVER UNOCCUPIED CUT-OUTS.
- PUSH-PIN MECHANISM ALLOWS EASY AND QUICK TOOL-LESS INSTALLATION.

## NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. INSERTION LOSS: 0.3dB MAX.
3. OPERATING & STORAGE TEMPERATURE -40°C TO +85°C
4. CERTIFICATIONS AND COMPLIANCES:

- ROHS
- GR-326-CORE
- TIA/EIA-568-C.3
- TIA-604-2A
- TIA-455 SERIES
- UL 94
- ASTM A1008
- IEC-61754-1



| Type #      | Mode   | Article # |
|-------------|--------|-----------|
| VFAP6SMMST  | MULTI  | 904-00377 |
| VFAP6SSMSTZ | SINGLE | 904-00378 |

|                       |                                                                                                                                                                                          |                                                                                                                                                                                                                             |                                                                                                        |     |           |                        |                                              |                |             |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|-----|-----------|------------------------|----------------------------------------------|----------------|-------------|
| Material<br>ASSEMBLED | Units: <b>inches</b><br>Dimension without tolerances details to:<br>.xxxx = ±.0005<br>.xxx = ±.005<br>.xx = ±.01<br>.x = ±.03<br>None = ±.06<br>∠ = ±0.5°<br>Dimension Formatted in [mm] | The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied, or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton. | Drawn                                                                                                  | GRW | 6/29/2016 | Article/Type-No        | VFAP6S_                                      | Scale          | 1:1         |
|                       |                                                                                                                                                                                          |                                                                                                                                                                                                                             | Approved                                                                                               | KAC | 6/29/2016 | Title                  | <b>FT ADAPTER PANEL WITH 6 ST CONNECTORS</b> | Project Number | PRP 16-1269 |
|                       |                                                                                                                                                                                          |                                                                                                                                                                                                                             | <b>HellermannTyton</b><br>North America<br>Email: corp@htamericas.com<br>Web: www.hellermann.tyton.com |     |           | Drawing-No             | PRODUCTION : Phase                           | Format         | AH          |
|                       |                                                                                                                                                                                          |                                                                                                                                                                                                                             |                                                                                                        |     |           | <b>16-1269-001-CSU</b> |                                              |                | Sheet 1/1   |