


CABLE ASSEMBLIES LONGER THAN 50FEET WILL BE WOUND ONTO A SPOOL LIKE THIS ONE. ONE END IS PROTECTED WITH BUBBLE WRAP, OPPOSITE END PROTECTED BY PLASTIC REEL, AND THE CABLE IS WRAPPED IN CARDBOARD. CABLE ASSEMBLIES LESS THAN 50 FEET WILL BE IN A BOX.



PRODUCT DESCRIPTION:

RNGC12AY _ H H XXX

- LENGTH IN FEET
- TERMINATION END 2
- TERMINATION END 1
- CABLE COLOR(BLUE OR WHITE)
- P OR R (PLENUM OR RISER)
- CABLE TYPE

INVENTORS	HellermannTyton® ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNITYTON	NOTES 1) PART NUMBER "RNGC12A Y _ H H XXX" : A = CAT6 UTP; Y = "P" OR "R"; (underscore) = CABLE COLOR (B = BLUE, W = WHITE) H = TERMINATION END 1 AND 2; XXX= 20 - 140FT.	REVISION DRAWING level 01 by AAC date 07/26/13 ECN # 012416 part level -	DIMENSIONS TOLERANCES .XXXX = ±.0005 .XXX = ±.005 .XX = ±.01 .X = ±.03 ∠ = ±0.5° unless otherwise specified units inches	PART number RNGC12AY_HHXXX phase Production name RAPIDNET LOOM 12 PORT CAT6 CASSETTE TO STAGGER PAIR JACK material ASSEMBLED	DRAWING format version N C CAD SW2011 scale 1:2 computer file name MI3026081CST_01 previous drawing number drawn AAC checked KAC approved 07/26/13 07/26/13 type CUSTOMER sheet 1 of 1 number MI3026081CST		
	name						date	city, state