



45740/45760 (ZW4003) Z-Wave Toggle Style In-wall On/Off Switch

45740 – White

45760 – Light Almond



Key Features

- Turn the connected device On/Off manually or via Z-Wave remote control.
- May be used in single pole installation or with up to three 45741(WH) or 45761(LA) (both ZW2003) auxiliary switches in 2-way, 3-way or 4-way wiring configurations
- Toggle style switch to match existing switches
- Can be included in multiple Groups and Scenes
- Supports Advanced Configuration; Invert switch (if unit is installed upside down)
- Screw Terminal installation; requires wiring connections for Line (Hot), Load, Neutral, and Ground. Traveler wire required for multi pole installation
- Use a standard-size wall plate for single gang installations (wall plate not included); Multi-gang box option available (removable 'side wings')
- White color (45740); Light Almond (45760)
- Inline traveler circuit protection
- White box contractor packaging

SPECIFICATIONS

Power: 120 VAC, 60 Hz.

Signal (Frequency): 908.42 MHz.

Load ratings:

Incandescent - Minimum Load: 40W, Maximum Load: 960W

Motor – 1/2HP

Resistive – 1800W

Range: Up to 100 feet line of sight between the Wireless Controller and the closest Z-Wave receiver module.

Operating Temperature Range: 32-104° F (0-40° C)

For indoor use only.

cUL Listed

Complies with FCC and Industry Canada regulations

JASCO Products

10 E. Memorial Rd

Oklahoma City, OK 73114

www.jascopeproducts.com

www.easyzwave.com

Z-Wave is a registered US trademark of Sigma Designs