

GEMC-Integrated 32 Point GEM-C Commercial Integrated Fire/Burg System Kit GEMC-COMBO32KT

- 24V Panel, 32 Points via commercial addressable, wireless or conventional fire or burg. devices, 2 on board NACs, 8 partitions (No Loop Isolator/Extender required)
- > 7 Amp, 24V Power Supply
- Burg. Module, with power supply with built in bus isolator for complete separation of fire and burg power and battery standby operation (GEMC-BM/PS)
- Built in horn/strobe synch. module on each NAC (Wheelock & System Sensor protocol)
- > Built in dual line communicator; dual onboard serial ports
- Quickloader up/downloading including remote smoke obscuration reporting
- > Locking, Large Red Enclosure, 16 x 25" reversible door, with 14.25" x 25" base (flush or surface mount.). Houses up to 32Ah battery backup.
- Menu-driven LCD Fire Annunciator (GEMC-FK1) mounts anywhere on bus (Also, full keyswitch support)



Napco Commercial GEMC Dedicated Burglary System Kits

96Pt Addressable Commercial Burglary System Kit GEMC-BURG96KT

- 24V Panel, 96 Points via commercial addressable, wireless or conventional burg. devices, 7 partitions
- Locking, Medium White Enclosure, 16 x 17" door, with 14.25" x 16" base (flush or surface mount.). Houses up to 16Ah battery backup.
- > 4 Amp, 24V Power Supply
- > Addressable SLC Burg Module, supports up to 96 addressable SLC burg devices (GEMC-BSLC)
- > Built in dual line communicator; dual onboard serial ports
- > Quickloader up/downloading
- Menu-driven LCD Burglary Keypad with built-in 4 zone EZM, mounts anywhere on bus (GEMC-BK1)

GEMC-ADBRG128 128pt GEMC Addressable Commercial Burglary System Kit, as above.

GEMC-ADBRG255 255pt GEMC Addressable Commercial Burglary System Kit, as above.

12VDC Burglary Power Supply for GEMC and Gemini Panels

GEMC-12V2PS-R 12VDC

- Power Supply for Burg. Bus of GEMC Panels, remote supervised.
- Powered by supplied 16.5V, 50VA plug-in transformer,
- > Supports 2ea. 12V, 7Ah standby batteries.
- > Backward compatible with all standard Gemini Panels, too.
- > Alarm Panel supervised power option

Note: Also available, Fire Bus Model with Direct 120VAC connection, model GEMC-12V2ASP-CF 12VDC

Add-on Napco Commercial Access option, see page 4



Wireless, UL Commercial, Peripherals

GEMC-REVC Wireless 255 point RF Receiver (4/system, max.) GEMC-WL-SMK Wireless Smoke, Photoelectric GEMC-WL-HEAT Wireless Heat, 135° F GEMC-WL-WD Wireless 1-pt input module GEMC-WL-WD2 Wireless 2-input module GEMC-WL-PIR Wireless 50' PIR GEMC-WL-DT Wireless 40' Dual Tech'y microwave/PIR GEMC-WL-GB Wireless Glassbreak

Wireless Gemini Commercial Carbon Monoxide Detector

GEMC-WL-CO, is a high-quality carbon monoxide (CO) detector with built-in supervised, digitally coded wireless transmitter and visual and audible alarm and low battery indicators. Designed for detection accuracy and reliability, it's part of both the Gemini and Gemini Commercial Grade wireless lines, and supported by Napco's GEM-RECV and Commercial GEMC-RECV Series Supervised Receivers, as part of GEMINI, GEMC & Eirowolf Alarm Systems. This con



GEMC & Firewolf Alarm Systems. This compact, white detector, with 5-3/8 diameter and 2" profile, uses a 3V Lithium Battery (CR123A) for long dependable product life. It will monitor alarms, restores, low battery, tamper and status, and is designed to meet or exceed today's rigorous life safety compliances, including testing to sensitivity limits specified in UL 2075, UL 2034.

Commercial Burglary Accessories and Options

GEMC-BM/PS Burg Module with 12V power supply provides isolated 4-wire burg bus for burg keypads and devices, plus 12V power output for aux. devices. Independent Burg. Bell output. Complete separation of fire and burg power, plus indep. burg. battery connection and charger for indep. burg. standby operation in power failure.

GEMC-BM Burg Module, isolated 4-wire burg bus for burg keypads and devices, plus 12V power output for aux devices. Indep. Burg bell output.

GEMC-BSLC Addressable SLC Burg Module, supports up to 128 addressable SLC burg devices. Up to 2 connect to GEM-C panel.

Burglary Peripherals

GEMC-BK1 LCD Burglary Keypad for Integrated. System, with 4-zone EZM built in (Requires GEMC-BM or BM/PS Module.)

GEMC-BSLC-4PT Addressable SLC 4 point input expansion module

GEMC-BSLC-1PT Addressable SLC 1 point input expansion module

GEMC-BSLC-DT Addressable SLC Commercial Dual Tech Microwave/ PIR, 40 x 40'

GEMC-BSLC-PIR Addressable SLC Commercial PIR, 50 x 50'

GEMC-BSLC-RLY Addressable SLC Commercial 1 point output module

GEMC-KOTAMPERKT Mercantile Tamper Kit, for large panel enclosures, supervised. (Not necessary if housing is recess-mounted.)

For Commercial Fire Peripherals & Options, see Firewolf section pg 3



(Note: Housing is white in color, not as shown.)