

PROFICIENT

# Protege

## Powered Subwoofers

### FS12 12" Floor Standing Sub

One dual-drive subwoofer with 12" front-firing polypropylene-coated fiber composite woofer, 12" down-firing passive radiator and Class D Amp with 300 watts RMS, 600 watts peak. Anti-clipping circuitry assures high output with low distortion. Black wood grain vinyl finish and dampened rubber feet.

- Amplifier Type: Class D Amp
- Power Rating Continuous: 300 Watts RMS
- Power Rating Peak: 600 Watts Peak
- Frequency Response: 28Hz - 150Hz
- Subwoofer Output: 106dB SPL
- Inputs: Left & Right Line Level, LFE
- Outputs: Line Level High-Pass

**ITEM**  
FS12      **U/M**  
Each

- Protection: Anti-Clipping Circuitry
- Power On/Off: Auto Sensing
- Phase Switch: 0 - 180°
- Crossover: 50Hz - 150Hz; Bypass
- Finish: Black Wood Grain Vinyl
- Dampened Rubber Feet
- Dimensions (H x W x D): 16<sup>5</sup>/<sub>8</sub>" x 14<sup>1</sup>/<sub>2</sub>" x 15<sup>1</sup>/<sub>2</sub>"



### FS10 10" Floor Standing Sub

One dual-drive subwoofer with 10" front-firing polypropylene-coated fiber composite woofer, 10" down-firing passive radiator and Class D Amp with 250 watts RMS, 500 watts peak. Anti-clipping circuitry assures high output with low distortion. Black wood grain vinyl finish and dampened rubber feet.

- Amplifier Type: Class D Amp
- Power Rating Continuous: 250 Watts RMS
- Power Rating Peak: 500 Watts Peak
- Frequency Response: 30Hz - 150Hz
- Subwoofer Output: 103dB SPL
- Inputs: Left & Right Line Level, LFE
- Outputs: Line Level High-Pass

**ITEM**  
FS10      **U/M**  
Each

- Protection: Anti-Clipping Circuitry
- Power On/Off: Auto Sensing
- Phase Switch: 0 - 180°
- Crossover: 50Hz - 150Hz; Bypass
- Finish: Black Wood Grain Vinyl
- Dampened Rubber Feet
- Dimensions (H x W x D): 15<sup>1</sup>/<sub>8</sub>" x 13<sup>1</sup>/<sub>4</sub>" x 14"

### FS8 8" Floor Standing Sub

One dual-drive subwoofer with 8" front-firing polypropylene-coated fiber composite woofer, 8" down-firing passive radiator and Class D Amp with 200 watts RMS, 400 watts peak. Anti-clipping circuitry assures high output with low distortion. Black wood grain vinyl finish and dampened rubber feet.

- Amplifier Type: Class D Amp
- Power Rating Continuous: 200 Watts RMS
- Power Rating Peak: 400 Watts Peak
- Frequency Response: 32Hz - 150Hz
- Subwoofer Output: 100dB SPL
- Inputs: Left & Right Line Level, LFE
- Outputs: Line Level High-Pass

**ITEM**  
FS8      **U/M**  
Each

- Protection: Anti-Clipping Circuitry
- Power On/Off: Auto Sensing
- Phase Switch: 0 - 180°
- Crossover: 50Hz - 150Hz; Bypass
- Finish: Black Wood Grain Vinyl
- Dampened Rubber Feet
- Dimensions (H x W x D): 13<sup>5</sup>/<sub>8</sub>" x 11<sup>3</sup>/<sub>4</sub>" x 12<sup>1</sup>/<sub>2</sub>"

