

TM SERIES 17"-22"

Economic Standard and Wide Screen High Resolution Displays



Model	TM17 (LCD)	TME19 (LED)	TME19W (LED)	TME22W (LED)
Screen Size	17"	19"	18.5" Wide	21.5" Wide
Aspect Ratio	4:3	4:3	16:9 & Opt 4:3	16:9 & Opt 4:3
Max Resolution	1280 x 1024	1280 x 1024	1366 x 768	1920 x 1080
Brightness	250cd/m ²	250cd/m ²	250cd/m ²	220cd/m ²
Contrast Ratio	1000:1	1000:1	1000:1	800:1
Response Time	5ms	5ms	5ms	5ms
Viewing Angle	150/140	170/160	170/160	170/160
Display Color	16.7M	16.7M	16.7M	16.7M
Power Consumption	<40W	<30W	<30W	<35W
Power	AC 120-240V	AC 120-240V	AC 120-240V	AC 120-240V
Input/Output	VGA DVI via adapter through HDMI (DVI to HDMI adapter is not included) HDMI BNC In BNC Out (when monitor is on with input selection at BNC In) Audio In Built-In Speakers	VGA DVI via adapter through HDMI (DVI to HDMI adapter is not included) HDMI BNC In BNC Out (when monitor is on with input selection at BNC In) Audio In Built-In Speakers	VGA DVI via adapter through HDMI (DVI to HDMI adapter is not included) HDMI BNC In BNC Out (when monitor is on with input selection at BNC In) Audio In Built-In Speakers	VGA DVI via adapter through HDMI (DVI to HDMI adapter is not included) HDMI BNC In BNC Out (when monitor is on with input selection at BNC In) Audio In Built-In Speakers
Speaker Output	3W + 3W	3W + 3W	3W + 3W	3W + 3W
VESA Mounting Holes	100mm x 100mm	100mm x 100mm	75mm x 75mm	75mm x 75mm
Dimensions (WxDxH)	15.55"x2.76"x15.36"	17"x2.76"x16.54"	18.46"x1.41"x14.25"	21"x1.41"x15.51"
Gross Weight	12.1 lb	11.2 lb	11 lb	13 lb

Specifications subject to change without notice

Also Available Are TME Series 24"-50" LED Digital Signage / CCVE Displays with USB Ports


TRIVIEW is a trademark of Tatung Company of America, Inc.