



Powerline 500 AV Nano Adapter Kit

TPL-406E2K (v2.0R)

- Includes two TPL-406E adapters
- Expand your network with this Powerline adapter
- Easy no-CD installation
- Two Powerline devices are required to start a network

TRENDnet's Powerline 500 AV Nano Adapter Kit, model TPL-406E2K, uses an electrical outlet to create a high speed network. Two adapters are needed to start a network. Connect one adapter to your router and plug another adapter into an outlet on your electrical system for instant high-speed network access. The compact form factor saves space around crowded electrical outlets. Use up to 8 adapters to network devices in different rooms without running new cabling.

Powerline



Adapters

Includes two TPL-406E adapters



Link Button

Press the Link button to change existing Powerline encryption keys



Pre-Encrypted

For your security the Powerline signal is pre-encrypted



Powerline 500

High speed Powerline networking over existing electrical lines



Ethernet Port

Convenient Ethernet port to hardwire computer, smart TV, or other network enabled device




Cross Compatible

Backward compatible with all Powerline 600, 500, and 200 adapters




Quick Setup

Get up and running in minutes with the intuitive guided setup




Plug In Install

Simply plug in TRENDnet adapters! The encrypted Powerline signal auto-connects over an existing electrical system.



No Clutter


The compact form factor stays off the ground by plugging directly into an outlet.



Ethernet Port

Ethernet port extends high performance wired connections.

Networking Solution



Specifications

Standards

- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3x
- IEEE 1901

Device Interfaces

- Ethernet port
- Link / reset button
- Status LEDs
- Power plug
 - A: North America Type B (NEMA 5–15)
 - EU: Euro Type C (CEE 7/16)
 - UK: United Kingdom Type G (BS 1363)

Frequency Band

- 2 – 68 MHz

Data PHY Rate

- Ethernet: up to 200 Mbps (Full Duplex mode)

Networking Distance

- Up to 300 m (980 ft.) linear distance over electrical power lines

Security

- 128-Bit AES (Advanced Encryption Standard)

Optional Utility: OS Compatibility

- Windows® 10, 8.1, 8, 7, Vista, XP

Nodes

- Up to 8 (max.)

Overlapping Powerline Networks

- Up to 4 (per electrical system)

Power

- Input: 100 – 240 V AC, 50/60 Hz
- Consumption: Active mode: 2.7 Watts (max.); Standby mode: 0.34 Watts (max.)

Operating Temperature

- 0 – 40 °C (32 – 104 °F)

Operating Humidity

- Max. 90 % non-condensing

Certifications

- CE
- FCC

Dimensions

- 68 x 55 x 28 mm (2.7 x 2.2 x 1.1 in.)

Weight

- A: 64 g (2.2 oz.)
- EU: 68 g (2.4 oz.)
- UK: 68 g (2.4 oz.)

Warranty

- 3 year limited

Package Contents

- 2 x TPL-406E
- Quick Installation Guide
- 2 x Network cable (1.5 m / 5 ft.)

