

Accessories

Mounting Kits							
Model Name	AM-525	AM-527	AM-528	AM-529	AM-52A	AM6101	AM6102
Description	Mounting adapter (3/4" NPT F and 1.5" PS11 M)	Mounting adapter (3/4" NPT F and 1.5" PS11 M)	Mounting adapter for outdoor dome (3/4" NPT F and 1.5" PS11 M)	Mounting adapter for speed dome (SD936x)	Mounting adapter for speed dome (SD916-H)	Wall Mount Kit for VS8401/VS8801	Rack Mount Kit for VS8401/VS8801

Mounting Kits				Enclosures			
Model Name	AM-712	AM-713	AM-714	AM-718	SP-702A	AE-201	AE-202
Description	Conduit Box	Conduit Box (Water-proof)	Junction box (Bullet)	Junction box	Mounting bracket	Indoor camera enclosure (Transparent cover)	Indoor camera enclosure (Smoke cover)

Enclosures							
Model Name	AE-211	AE-232	AE-234	AE-235	AE-238	AE-239	AE-243
Description	Outdoor enclosure with blower (90-240V AC input)	Outdoor enclosure with blower/heater (90-240V AC input)	Outdoor enclosure with fan/heater, IR, IK10 (90-240V AC input)	Outdoor enclosure with fan/heater, IR (90-240V AC input)	Value series enclosure 24VAC/VDC input, IP68, IK10	Value series enclosure, PoE input, IP68, IK10	Value series enclosure, built-in fixed 50M IR, 24VAC/VDC input, IP68, IK10

Enclosures							
Model Name	AE-244	AE-23A	AE-23B	AE-23C	AE-23D	AE-23E	AE-23F
Description	Value Series Enclosure, built-in fixed 50M IR, PoE input, IP68, IK10	Supreme series enclosure, optional VAIR illuminator, 24VAC/VDC input, IP68, IK10	Supreme series enclosure, wiper, optional VAIR illuminator, 24VAC/VDC input, IP66, IK10	Supreme series enclosure, cold start heater, optional VAIR illuminator, 24VAC/VDC input, IP68, IK10	Supreme series enclosure, wiper, cold start heater, optional VAIR illuminator, 24VAC/VDC input, IP66, IK10	Supreme series enclosure, optional VAIR illuminator, PoE input, IP68, IK10	Supreme series enclosure, wiper, optional VAIR illuminator, PoE input, IP66, IK10

Enclosures			Dome Covers				IR Illuminators
Model Name	AE-251	AE-252	AC-215	AC-227	AC-228	AC-229	AI-106
Description	Outdoor dome housing with fan/heater (transparent cover) (DC 12V input)	Outdoor dome housing with fan/heater (Smoke cover) (DC 12V input)	Smoked cover (Indoor speed dome)	Transparent cover for CU8131, FD816C(A)-HF2	Transparent cover for CU8171, FE8182	IK10 Transparent cover for recessed-mount cameras	VAIR illuminator 6W for Supreme series enclosure, adjustable beam angle 10°-40°, 25-100M, -40°C-50°C

Accessories

IR Illuminators		Lenses		Power Adapters			
Model Name	AI-108	AI-109	AL-244	AL-245	AA-221	AA-231	AA-341
Description	VAIR illuminator 24W for Supreme series enclosure, adjustable beam angle 10°-30°, 80-160M, -40°C-50°C	VAIR illuminator 48W for Supreme series enclosure, adjustable beam angle 10°-30°, 120-200M, -40°C-50°C	C mount, 4-18 mm, F1.4, P-iris, 1/1.8	CS mount, 12-40 mm, F1.8, P-iris, 1/1.8	DC 12V 1.5A power adapter	DC 12V 2.5A power adapter	AC 24V 3.5A power adapter

Network Accessories		Joystick		Cable		Storage	
Model Name	AN3000	AJ-001	AJ-002	AO-001	AO-002	AO-003	SR-64VMA/T1
Description	Outdoor Ethernet waterproof connector	8-key USB Joystick	29-Key USB JoyStick	I/O Cable for speed dome	RJ45 to M12 (4-pin) water-proof Cable (1 meter)	I/O Cable for speed dome	Sony 64GB SD Card (Individual Pack w/ SD Card Adapter)

Mounting Installation

		Outdoor	Bullet Cameras	180° Cameras
Application	Model	IB836BA Series IB8382 Series IB9371 Series IB9381 Series	IB8367A IB8369A IB8377-H IB8379-H	MS8391-EV
Pole Mount Adapter		•		•
Adapter Plate			•	
Junction Box		•		