

ClickShare CSC-1

Full-featured wireless presentation system for high-profile meeting rooms and boardrooms



ClickShare is Barco's wireless presentation and collaboration system, that allows any meeting participant to share content on the central meeting room screen.

An unmatched user experience

At the click of a button, the content of your laptop, tablet or smartphone is displayed on the large screen. The result is that all participants are involved more intensely in the decision-making process. Coupling extreme simplicity with an unmatched user experience, everybody who has used ClickShare is immediately hooked. The system's stability and ease-of-use, also drastically limits the number of needed interventions by the IT department.

More pixels, more content

If you are driving two projectors, two screens, or Double HD canvas, the full-featured CSC-1 Base Unit is the right choice. This unit is fully compatible with the ClickShare Buttons and the apps for mobile devices, and was optimized for use in high-profile meeting rooms and boardrooms.

Optimized collaboration experience

By enabling to display the content of up to 4 users simultaneously, the CSC-1 Base Unit brings a complete Clickshare collaboration experience. 64 Buttons can be wirelessly connected to the Base Unit, ready to share. Furthermore, perfectly synchronized sound and video ensures that movie clips can be optimally enjoyed. And dynamic content from iPads, iPhones and Samsung Galaxy devices can be shown directly to the screen using the specialized apps. For other Android devices, you are restricted to showing static content.

PRODUCT SPECIFICATIONS**CLICKSHARE CSC-1**

General specifications	
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 10.3 / Mac OS 10.11 El Capitan or higher
Operating system	Windows 7/8/8.1/10 32 & 64 bit Mac OSX 10.10/10.11/10.12 (Sierra) Android v5 & v6 (ClickShare app) iOS 8, 9 & 10 (ClickShare app)
Video outputs	DisplayPort, Single link DVI-I VGA (via included convertor, highest resolutions only with reduced blanking) In "Dual screen" mode, connection can occur either through DVI and DisplayPort, or through VGA and DisplayPort.
Frame rate	Up to 30 fps (from software version V1.03.00.0001 onwards)
Output resolution	UHD (3840 x 2160) available from ClickShare CSC Base Unit software v01.09.00.22 onwards
Noise Level	Max. 28dBA
Number of sources simultaneous on screen	4
Number of simultaneous connections	64
Audio	Analog audio from ClickShare CSC Base Unit software v01.02.00.09 onwards Digital audio (embedded in DP signal) from ClickShare CSC Base Unit software v01.05.00.32 onwards
iPad, iPhone and Android compatibility	Available via ClickShare app for static content. For iOS devices using iOS9, full mirroring is possible from ClickShare CSC Base Unit firmware v01.09.00.22 onwards
Extended desktop	Available (depending on the driver of your graphics card)
Authentication protocol	WPA2-PSK
Encryption	AES CCMP
Wireless transmission protocol	IEEE 802.11 a/g/n
Data rate wireless	Up to 300Mbps
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 4x (back) + 1x (front) USB Analog line out on mini jack socket (3.5mm) Analog line in on mini jack socket (3.5mm)
Temperature range	Operating: +5°C to +40°C (+41°F to +104°F) Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Altitude	Max 3000m (9842 ft)
Lifetime	MTBF = 40,000h (90% confidence level) MTBF = 100,000h (60% confidence level) MTBF conditions: ■ Environment: Ground Benign ■ Temperature: 25°C ■ Method: MIL-HDBK-217F Notice 2
Warranty	3 years standard Possible to extend to 5 years

PRODUCT SPECIFICATIONS

CLICKSHARE CSC-1

System requirements

PC minimum requirements:

- CPU: Intel Pentium Dual Core E2140 – 2 * 1600 Mhz (or equivalent: AMD Athlon 64 X2 3800+ - 2 * 2000 Mhz)

- Memory: 1024 MB RAM

- OS: Windows XP Pro/Home (SP3) (Windows Vista/7 supported, but requires more RAM)

PC recommended requirements:

- CPU: Intel Core 2 Duo E4600 – 2 * 2400 Mhz (or equivalent: AMD Athlon 64 X2 4800+ - 2 * 2500 Mhz)

- Memory: 2048 MB RAM

- OS: Windows XP Pro/Home, Windows Vista, Windows 7, Windows 8

MAC

- CPU: Intel Core 2 Duo

- Memory: 2048 MB RAM

- OS: Mac OS X 10.6, 10.7, 10.8

ClickShare Base Unit dimensions

Dimensions (HxWxD)

181mm (incl. antennas) x 260mm x 276mm (Min.) / 7.125" (incl. antennas) x 10.236" x 10.9" (Min.)

Power consumption

Shutdown: 2.5W

Operation (typical): 20W

Maximum: 35W

Weight

2.6 kg/5.75 lb

Last updated: 04 Jul 2017

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.