



Price* : 12.70 USD



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ
Associated head	ZCKE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal (-)
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	50...248 °F (10...120 °C) high temperature -40...158 °F (-40...70 °C) low temperature -13...158 °F (-25...70 °C) standard environment
Ambient air temperature for storage	-40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature -40...158 °F (-40...70 °C) standard environment
Environmental characteristic	Low temperature Standard environment High temperature

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
----------	---------------------------------

Discount Schedule	T
GTIN	00785901646303
Nbr. of units in pkg.	1
Package weight(Lbs)	5.999999999999998E-2
Returnability	Y
Country of origin	ID

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------