

---

## TRULINK®; 2-PORT UXGA MONITOR SPLITTER/EXTENDER (FEMALE INPUT)

2006-29503-ADT | [Quiktron](#)



---

### FEATURES & BENEFITS

Distribute any video signal to 2 different video outputs, while maintaining vivid picture quality. Though powerful, this splitter is easy to use; just connect the cables, and you're ready to go! There is no software required, or complicated interface cards to install. This monitor splitter not only distributes, but also boosts your high resolution video signal up to 210 feet.

#### Video Specifications

- Signal Types Supported - VGA, SVGA, XGA, UXGA, and MultiSync®
- Video Bandwidth - 350MHz
- Maximum Resolution Supported - 1920 x 1440 at 80Hz
- Maximum Cable Length Supported - 210ft

#### Power Adapter Specifications

- Power Input - 100-240VAC ~ 50-60Hz
- Power Output - 9VDC, 600mA
- Pin Diameter - 5.5mm
- Center Pin Polarity - Positive

#### Physical Characteristics

- Video Input Connector - HD15 Female
- Video Output Connectors - HD15 Female
- Housing Material - Metal
- Dimensions - 7.25 x 0.75 x 3.25in

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black  
Number Of Ports: 2  
Product Series: TruLink  
Type: VGA Splitters