

R615DC1016 Series DC CCTV Rack Power Supplies

Description

Altronix R615DC1016 Series Rack Mount CCTV Power Supplies provide 6-15VDC distributed via sixteen (16) fuse or PTC protected outputs for powering CCTV cameras, heaters, and other video accessories.



R615DC1016CB

Key Features

- Sixteen (16) fuse or PTC protected outputs.
- 6-15VDC output voltage.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.
- Sixteen (16) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.
- Spare fuses provided.
- CE Approved.
- Lifetime Warranty / Made in the U.S.A.

R615DC1016 Series Power Supply Configuration Reference Chart

Altronix Model Number	Total Output Current	Output Voltage	Number of Outputs	PTC Protected Outputs (auto-resettable)	Fuse Protected Outputs	Output Current (max per output)	115VAC 50/60Hz Input Current
R615DC1016	10A	6-15VDC	16	—	✓	3.5A	1.9A
R615DC1016CB				✓	—	2.5A	

Specifications

Input

Voltage 115VAC, 50/60Hz, 1.9A.

Outputs

Voltage 6 - 15VDC.
Current 10A total output current.
Protection Fused 3.5A / PTC 2.5A.

Indicators (LED)

Output Sixteen (16) individual LEDs.

Agency Listings

CE European Conformity

Physical and Environmental

2U rack mount chassis for use in standard EIA 19" rack.

Dimensions (H x W x D):

3.26" x 19.125" x 8.5" (83mm x 486mm x 216mm).

Product Weight 17.15 lbs. (7.78 kg).

Shipping Weight 18.15 lbs. (8.23 kg).

Temperature:

Operating 0°C to 49°C (32°F to 120°F).

Storage -20°C to 70°C (-4°F to 158°F).

Relative Humidity 85% +/-5%.

BTU/Hr. (approx.): 46-77 BTU/Hr.