

PIXIM
EVERY PIXEL TELLS A STORY
Select models



Gang box not included



White, silver and Ivory faceplates included

Speciality Cameras

In Wall Camera Kits

GBK Series

Ganz gang box camera kits are designed to fit into most single electrical boxes, making them ideal for discrete surveillance in a wide range of environments. The kits include a white, ivory and silver faceplate as well as a clear and tinted window. Two camera options are available, a 690 TVL **Pixim Seawolf WDR** camera for tough backlight applications and a 700TVL camera for standard interior use. The camera can be tilted and swiveled inside the gangbox to achieve the desired angle of view. Both models include a day/night mode for excellent low light performance.

Features:

- 690 TVL Pixim Seawolf WDR and 700 TVL standard models
- 3.6mm lens standard (other lens options available)
- Tamper-Resistant mounting screws
- 3 faceplates included (white, silver and ivory)
- Clear and tinted windows included
- Fits most single gang electrical boxes (not included)
- 12VDC Power Input



CBC AMERICA Corp.

Scan Me!



GBK Kits

In Wall Camera Kits

Expanded and Dimensional Views



Specifications

General	GBK-36W	GBK-36X
Image Picture Element	 Pixim Seawolf Sensor	1/3" 960H Super HAD CCD II (Sony)
Resolution	690TVL (Horizontal)	700TVL (Horizontal)
Effective Pixels	758 (H) x 540 (V)	976 (H) x 494 (V)
Scanning System	2:1 Interlace	
Lens	3.6mm wide angle fixed (Horizontal Angle of View 71.2°)	
Functional		
Wide Dynamic Range	120 db (102 dB typical)	-
White Balance	ATW, AWB, Manual	ATW, Push, User1, User2, Anti CR, Manual, Push Lock
Day/Night Function	Digital Day/Night	
OSD	Yes (Multi-Language)	
Image Flip	Yes	On/Off
Motion Detection	On/ Off, 4 Programmable zones	On/Off (4 areas)
Backlight Compensation	Off/ On, adjustable backlight zone	BLC / HLC / Off
Shutter Speed	1/25-1/30,720 sec	1/60 ~ 1/100,000 sec
Digital Slow Shutter	Off / 2x-32x	-
Minimum Illumination	0.1 lux @ F1.2	0.1Lux @ F2.0
AGC	Up to 50dB	Off / 0.25 / 0.50 / 0.75 / 1.00
S/N Ratio	Up to 53dB Digital	50dB or more (AGC Off)
Physical/Additional		
Power Input	12VDC	
Power Consumption	4.2W max.	80mA max
Faceplate Dimensions	4.5" H x 2.8" W x 1.6" D	
Weight	Approx. 0.1lbs (50g)	
Operating Temperature	14° ~ 122° F (-10° ~ 50° C)	
Storage Temperature	-4° ~ 140° F (-20° ~ 60° C)	
Face Plates	Three included: White, Silver and Ivory	
Window Lens	Two included: Clear and Tinted	

All specifications are subject to change without notice