

Structured Wiring Enclosures

Structured wiring enclosures from Channel Vision Technology are designed to be the central “brain” of the home sending signals to every room, with distribution from cable TV, satellite, speakers, IR, fiber optics, telephone, automation, internet, security cameras, and much more. The modular layout of these sturdy cabinets allow easy access and is upgradeable. Plus, with sizes of 12”, 19”, 28”, 38”, and 50” Channel Vision has an enclosure to fit any need.

Features
UL Approved
Modular Push and Lock Product Components
Electrical Gang Box Knockout with Grounding Screw
Sturdy 18 gauge Steel Construction
Powder Coated White Paint
Includes Wire Management Straps, Large Cable Knockouts, Grommets, Cable Identifiers, and Cardboard Rough In Cable Protector



12" Enclosure (C-0112E)	19" Enclosure (C-0119E)	28" Enclosure (C-0128E)	38" Enclosure (C-0138E)	50" Enclosure (C-0150E)
Dimensions: 12"(L) x 14"(W) x 3 5/8(D) Material: C.R.S Gauge: 18 awg Indoor / Outdoor: Indoor Use Knockout Size: 1 3/4" Electrical knockout: Single Gang Knockout Top: 5 Knockout Box: 3 Knockout Sides: 1 each side	Dimensions: 19"(L) x 14"(W) x 3 5/8(D) Material: C.R.S Gauge: 18 awg Indoor / Outdoor: Indoor Use Knockout Size: 2.36" Electrical knockout: Single Gang Knockout Top: 5 Knockout Box: 3 Knockout Sides: 1 each side	Dimensions: 28"(L) x 14"(W) x 3 5/8(D) Material: C.R.S Gauge: 18 awg Indoor / Outdoor: Indoor Use Knockout Size: 1 3/4" Electrical knockout: Single Gang Knockout Top: 5 Knockout Box: 3 Knockout Sides: 5 each side	Dimensions: 38"(L) x 14"(W) x 3 5/8(D) Material: C.R.S Gauge: 18 awg Indoor / Outdoor: Indoor Use Knockout Size: 1 3/4" Electrical knockout: Single Gang Knockout Top: 5 Knockout Box: 3 Knockout Sides: 5 each side	Dimensions: 50"(L) x 14"(W) x 3 5/8(D) Material: C.R.S Gauge: 18 awg Indoor / Outdoor: Indoor Use Knockout Size: 1 3/4" Electrical knockout: Single Gang Knockout Top: 5 Knockout Box: 3 Knockout Sides: 5 each side
12" Enclosure Covers	19" Enclosure Covers	28" Enclosure Covers	38" Enclosure Covers	50" Enclosure Covers
Screwdown Cover: C-0112C Hinged Cover: N/A Double Door: N/A Designer Door: N/A	Screwdown Cover: C-0119C Hinged Cover: C-0119HC Double Door: N/A Designer Door: N/A	Screwdown Cover: N/A Hinged Cover: C-0128HC Double Door: N/A Designer Door: C-0128D	Screwdown Cover: N/A Hinged Cover: C-0138HC Double Door: C-0138DD Designer Door: C-0138D	Screwdown Cover: N/A Hinged Cover: C-0150HC Double Door: N/A Designer Door: C-0150D

Enclosure Accessories



Extension Ring
50" - 1.75" depth
C-1351



Brackets
Horizontal - C-0308
Vertical - C-0309



Universal Mounting Plastic
Plate w/ Standoffs
C-1327



Product Holders
6-3/8 x 3-1/4" - C-1311
11-3/4 x 3-1/4" - C-1312



Grid Lifting Wire
Chase Module
C-1320



Hinged Expansion
for use w/ C-1351
C-1321




Replacement Lock & Key
C-1352:19,28,38HC
C-1350:C0150HC



Snap Pin Mini-Grip
C-1302



Fan Kit (Designer Doors)
C-1322



Mounting Clips for 3/8,
1/2 & 5/8" Drywall on Steel Studs
C-1328, C-1329, C-1330

*Specifications subject to change. iOS and Android are registered trademarks of their respective companies.



Surveillance Systems



Structured Wiring



Intercom & Telephone
Entry Systems



IR Remote Control
Distribution



Audio & Video
Distribution



www.channelvision.com

Toll Free: 800.840.0288

Local: 714.424.6500

234 Fischer Ave. Costa Mesa, CA 92626 USA