

33VDC POWER SUPPLY UNIT FOR IKALL ENTRANCE PANEL

Power supply unit with 110-230V primary and 33Vdc 500 mA continuous output, and 1.2A inrush current for external unit with IKALL entrance panel. Equipped with internal protection against overcurrent and short circuits. Dimensions: 71.7x90x62 mm (4 DIN modules).



General specifications

Input voltage AC:	110÷230Vac
Output voltage DC:	33V
Applicable to DIN rail:	Yes
Number of DIN modules:	4
Max. current delivered (A):	1,2

General info

Product height (mm):	62
Product width (mm):	71,7
Product depth (mm):	90
Operating temperature (°C):	0 ÷ 30

Compatibility

Simplebus Top system:	Yes
Simplebus Color system:	Yes

Electrical specifications

Maximum current absorption (mA):	800
----------------------------------	-----