

MT-8006B Data Diver



PBX Pause



Hands-free



Tone & Pause



Polarity Test



Last Number Redial



LCD display w/ backlight

LCD display with backlight function allows for data reading in dark areas

Talk / Monitor

High impedance monitor for data safe operation without disrupting existing traffic

Polarity indication

Identify the telephone line polarity easily

Smart power saving

Smart power saving enables battery life up to 6 months

Hands-Free

Headset provides convenient hands-free function

ELECTRICAL

Loop limit	2 K Ω maximum at 48 Vdc (nominal 20 mA minimum loop current)
------------	--

DC resistance

Talk Mode	300 Ω typical
Monitor impedance	>39k Ω nominal at 1 KHz

Rotary dial output

Pulsing rate	10pps+0.8pps
Percent break	60/40%±2%
Inter digit interval	1000 ms typical
Leakage during Break	>130 K Ω

DTMF output

Tone frequency error	±1.5% maximum
Tone level	-8±2dBm combined (typical)
High versus low tone	4 dB maximum

Memory dialing

Memory capacity	12 memories
Digit capacity	16 digits per memory
PBX pause duration	1~3.6 seconds
Power source	4pcs 1.5V AAA batteries (not included)

PHYSICAL(Hook included)

Measurement	218.5 × 69.5 × 49mm (8.6" × 2.7" × 1.9")
Weight	208g typical



Telephone line testing



High impedance monitor



Accessories

Picture for reference only. Please check with distributor for exact offers. All specifications are subject to change without notice.

Pro'sKit®



Eclipse Enterprises, Inc.
13302 Chula Road, Amelia Court House, VA 23002
Phone: 804-561-2610 Fax: 804-561-2642
Web Site: www.eclipseetools.com
©2013 Pro'sKit Industries Co., LTD. All rights reserved 201301