



712



712-75



732



732-75

700 Series

The industrial grade, **fire-rated solution** for high abuse applications

The 700 series is a 3 hour fire-rated, industrial grade electric strike designed for extreme heavy duty applications. The all stainless steel construction of this device makes it ideal for high abuse applications. The 712 series is designed to accommodate 1/2" throw latchbolts, and the 712-75 is designed to accommodate 3/4" latchbolts.*

712

For use with 1/2" to 5/8" throw latchbolts in hollow metal frame applications

1/2" PK keeper standard

712-75

For use with 1/2"**, 5/8"*** or 3/4" throw latchbolts in hollow-metal frame applications

3/4" PK keeper standard

732

For use with 1/2"*** to 5/8"*** throw latchbolts in wood frame applications. Features an offset solenoid

PK keeper standard

732-75

For use with 1/2", 5/8" or 3/4" throw latchbolts in wood frame applications. Features an offset solenoid

3/4" PK keeper standard

*NOTE: These products will require relocation of the center line when used with moritse locks. Consult HES customer support regarding use with the Best 40 series.

**NOTE: When using LBMLCM with a 1/2" or 5/8" keeper latchbolt detection may be dependent on the door gap.

Specifications

- UL 10C fire-rated, 3-hour single door (fail secure only)
- UL 10C fire-rated, 3-hour double door (fail secure only)
- CAN4-S104 (ULC-S104) fire door conformant
- UL 1034, burglary-resistant listed
- UL 294 (6th Edition) listed
- ANSI/BHMA A156.31, Grade 1
- New York City accepted
- NFPA-252 fire door conformant
- ASTM-E152 fire door conformant
- RoHS compliant

Electrical (continuous duty)

- .29 Amps at 12 VDC
- .15 Amps at 24 VDC
- PoE friendly

Standard Features

- Tamper-resistant, heavy duty construction
- Constructed entirely of stainless steel for strength and corrosion resistance
- Static strength 1,500 lbs.
- Dynamic strength 70 ft-lbs.
- Horizontally adjustable keeper allows for door and frame misalignment
- 1/2" keeper depth (712 and 732)
- 3/4" keeper depth (712-75 and 732-75)
- Non-handed
- Fail secure
- Plug-in connector
- Five-year limited warranty

Optional Features

- Fail safe

LBMLCM » Latchbolt & Locking Cam Monitor

Accessories

- 150** » Strike latch guard
152 » Universal mounting tabs
2001-1 » Wire-in bridge rectifier
2001M » Plug-in bridge rectifier
2004M » ElectroLynx® adapter
2005M3 » SMART Pac® III
2006M » Plug-in buzzer

Finishes

- 630** » Satin stainless steel
605 » Bright brass
606 » Satin brass
612 » Satin bronze
613 » Bronze toned
629 » Bright stainless steel



CYLINDRICAL
LOCKSETS



MORTISE LOCKS
WITHOUT
DEADBOLTS



FIRE RATED



GRADE 1



UL 1034
BURGLARY
LISTED

