

Digital Video Recorder

Model	Video Comp.	Video Input/ Output	Audio Input/ Output	Resolution	Frame Rate	VGA Resolution	Internal SATA	USB	Alarm Input/ Output	Power
DS-7308HFI-ST	H.264	8-ch / 2-ch	4-ch / 1-ch	4CIF	30fps	1920x1080 (HDMI) 1920x1080 (VGA)	DVD-R/RW + 3 HDD Max (4TB each)	3	8-ch / 4-ch	100-240V, 60 Hz <50W (w/o HDD)
DS-7316HFI-ST		16-ch / 2-ch	4-ch / 1-ch	4CIF	30fps				16-ch / 4-ch	
DS-7304HFI-SE	H.264	4-ch / 2-ch	4-ch / 1-ch	4CIF	30fps	1024x768	1 SATA (2TB each)	2	4-ch / 1-ch	12VDC, 3A <18W (w/o HDD)
DS-7204HVI-ST	H.264	4-ch / 2-ch	4-ch / 1-ch	4CIF 2CIF CIF	12fps 12fps 30fps	1024x768	1 SATA (2TB each)	2	4-ch / 1-ch	12VDC, 3A <18W (w/o HDD)
DS-7208HVI-ST	H.264	8-ch / 2-ch	4-ch / 1-ch	4CIF 2CIF CIF	8fps 8fps 30fps	1024x768	Up to 2 SATA (2TB each)	2	8-ch / 4-ch	12VDC, 3A <18W (w/o HDD)
DS-7216HVI-ST	H.264	16-ch / 2-ch	4-ch / 1-ch	4CIF 2CIF CIF	6fps 6fps 30fps	1024x768	Up to 2 SATA (2TB each)	2	16-ch / 4-ch	12VDC, 3A <18W (w/o HDD)

HDD

Model	Description
HK-HDD500GB	500GB SATA HDD
HK-HDD1T	1T SATA HDD
HK-HDD2T	2T SATA HDD
NEW HK-HDD3T	3T SATA HDD

Digital Video Server

Model	Video In	Video Out	Audio In/Out	Voice Talk Input	Resolution	Dual Stream	Network Interface	RS-232	RS-485	Alarm Input/ Output	Power
DS-6101HFI-IP-SD	1-ch	—	1-ch / 1-ch	1-ch	4CIF@30fps	Yes	Yes	Yes	Yes	1-ch / 1-ch	12VDC (<3W)
DS-6604HFI	4-ch	—	4-ch / 1-ch	1-ch	4CIF@30fps	Yes	Yes	Yes	Yes	4-ch / 2-ch	12VDC (<8W)
DS-6508HFI	8-ch	—	8-ch / 1-ch	1-ch	4CIF@30fps	Yes	Yes	Yes	Yes	16-ch / 4-ch	100 - 240V 6.3A <40W
DS-6516HFI	16-ch	—	16-ch / 1-ch	1-ch	4CIF@30fps	Yes	Yes	Yes	Yes	16-ch / 4-ch	100 - 240V 6.3A <40W

Keyboard

Model	Control Mode	LCD Screen	Joystick	Decoding Resolution	USB	Network Interface	RS-485	Power
DS-1003KI	RS-485	5"x2.5"	3 - Axis	No	No	No	Yes	12 VDC (<10W)
DS-1100KI	Network	7" TFT touch screen at 800x480 resolution	3 - Axis	1920x1080P	Yes	Yes	Yes	12 VDC (<15W)