

J&A AUDIO™

Better sound quality, **Better** features, **Better** price,

Just without the

B-WORD

logo.



*Speakers to Fit Every Need,
and Every Lifestyle.*



An Intrasonic Technology Company



The sound quality from our products is continually tested against the competition, and we beat them every time. To keep this edge, we observe every stage of production in painstaking detail. From superior materials, design flexibility, reliability and efficiency to quality sound reproduction, we make no compromises. Moreover, we're experts in the delivery of aesthetically pleasing products at a reasonable price. We understand what customers need from a manufacturer like JA Audio, and we make those needs our prime directive.

Don't settle for less, choose JA Audio.

I30C

Watts/RMS: 30
 Mounting: Cam-Lock
 Grille: White Metal
 Frequency: 48 Hz - 20 kHz
 Overall Dimensions: 9 1/2" DIA x 3" DPT
 Install Dimensions: 7 1/2" DIA
 Tweeter Type and Size: Mylar 1/2"
 Magnet Weight: 10 oz
 Cone Type and Size: 6 1/2" Coated Paper
 Db Sensitivity: 88 db
 Impedance: 8 Ω nominal
 Speaker Bracket: SPKBKT-6C
 Warranty: IntraSonic 10 Year



I100C

Watts/RMS: 100
 Mounting: Cam-Lock
 Grille: White Metal
 Frequency: 36 Hz - 22 kHz
 Overall Dimensions: 10 3/4" DIA x 3 1/2" DPT
 Install Dimensions: 9 1/4" DIA
 Tweeter Type and Size: 360° Directional Laminated Alum PP1
 Magnet Weight: 13.3 oz
 Cone Type and Size: 8" Laminated PP
 Db Sensitivity: 89 db
 Impedance: 8 Ω nominal
 Bass and Treble: 3 Position Adjustable
 Speaker Bracket: SPKBKT-8C
 Warranty: IntraSonic 10 Year



EX-206C

Power Handling: 5~100
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 55 Hz - 22,000 Hz
 Overall Dimensions: 9 1/8" DIA x 5 1/4" DPT
 Install Dimensions: 8 3/8" DIA
 Cone Type and Size: 6.5" Yellow Fiberglass Cone with a Rubber Surround
 Crossover: Hi-End 18 dB, Adjustable for Tweeter Level \pm 3 dB
 Angel Degree: 20
 Tweeter: 1" Titanium Dome Swivel
 Efficiency: 89 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-6C
 Warranty: IntraSonic 10 Year



EX-R6T

Power Handling: 5~100
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 52 Hz - 22,000 Hz
 Overall Dimensions: 11" DIA x 6" DPT
 Install Dimensions: 9 1/4" DIA
 Cone Type and Size: Pivoting 6.5" Yellow Fiberglass Cone with a Rubber Surround
 Crossover: Hi-End 12 dB, Adjustable for Tweeter & Woofer
 Woofer: Level \pm 3 dB
 Tweeter: Pivoting 1" Titanium Dome Swivel
 Efficiency: 88 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-8C
 Warranty: IntraSonic 10 Year



EX-C80II

Power Handling: 45~150
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 40 Hz - 20 kHz \pm 3 dB
 Overall Dimensions: 10 3/4" DIA x 5 1/4" DPT
 Install Dimensions: 9 1/2" DIA
 Cone Type and Size: 8" Yellow Fiberglass Cone with Rubber Surround
 Crossover: Hi-End 12 dB, Adjustable for Tweeter & Woofer
 Tweeter: 1" Titanium Dome Swivel
 Tweeter with Ferro fluid Cooled Voice Coil
 Db Sensitivity: 88 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-8C
 Warranty: IntraSonic 10 Year



EX-C65

Power Handling: 5~100
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 50 Hz - 22,000 Hz
 Overall Dimensions: 9" DIA x 4" DPT
 Install Dimensions: 8" DIA
 Cone Type and Size: 6 1/2" Yellow Fiberglass Cone with a Rubber Surround
 Crossover: Hi-End 18 dB, Adjustable for Tweeter & Woofer \pm 3 dB
 Tweeter: 1" Titanium Dome Swivel
 Db Sensitivity: 90 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-6C
 Warranty: IntraSonic 10 Year



JA-C8AII

Power Handling: 10~150
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 42 Hz - 22,000 Hz
 Overall Dimensions: 11" DIA x 3 1/2" DPT
 Install Dimensions: 9 1/2" DIA
 Cone Type and Size: 8" Aluminum Cone with a Rubber Surround
 Crossover: 18 dB High - Low pass
 Adjustable Crossover: Tweeter 0/-3 dB
 Tweeter: 1" Aluminum Dome Swivel With Ferrofluid Cooled Voice Coil
 Efficiency: 91 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-8C
 Warranty: IntraSonic 10 Year



JA-C6AII

Power Handling: 10~100
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 50 Hz - 22,000 Hz
 Overall Dimensions: 9 1/2" DIA x 3 1/8" DPT
 Install Dimensions: 8" DIA
 Cone Type and Size: 6 1/2" Aluminum Cone Woofer with a Rubber Surround
 Crossover: 18 dB High - Low pass
 Adjustable Crossover: Tweeter 0/-3 dB
 Tweeter: 3/4" Aluminum Dome with Ferrofluid Cooled Voice Coil
 Efficiency: 89 db
 Impedance: 8 Ω nominal
 Speaker Bracket: SPKBKT-6C
 Warranty: IntraSonic 10 Year



EX-CC6

Power Handling: 35~100
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 52 Hz - 22,000 Hz
 Overall Dimensions: 20 1/4" L x 9" H x 4" DPT
 Install Dimensions: 18 3/4" L x 7 3/8" H
 Cone Type and Size: (2) 6 1/2" Yellow Fiberglass Cone with a Rubber Surround
 Crossover: Hi-End 12 dB, Adjustable for Tweeter & Woofer Level \pm 3 dB
 Tweeter: 1" Titanium Dome Swivel
 Efficiency: 88 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: N/A
 Warranty: IntraSonic 10 Year



The JA Audio Warranty

JA Audio will repair or replace any defect in material or workmanship which occurs during normal use of every product with new or rebuilt part, free of charge in the USA, ceiling, in-wall speakers and outdoor speakers 10 (ten) years and 2 (two) years for subwoofers from the date of original purchase. This warranty does not cover damages in shipment, failures caused by other products not supplied by JA Audio, or failures due to accident, misuse, or alteration of the equipment. This warranty is extended only to the original purchaser, and a purchase receipt invoice or other proof of original purchase date will be required before warranty repairs are provided.

JA-CC5AII

Power Handling: 10~100
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 70 Hz - 22,000 Hz
 Overall Dimensions: 17 3/4" L x 8 3/4" H x 3" DPT
 Install Dimensions: 16 3/8" L x 7 3/8" H
 Cone Type and Size: (2) 5 1/4" Aluminum Cone with a Rubber Surround
 Crossover: 18 dB High - Low Pass
 Adjustable Crossover: Tweeter 0/-3 dB
 Tweeter: 3/4" Aluminum Dome Tweeter with Ferrofluid Cooled Voice Coil
 Efficiency: 89 db
 Impedance: 8 Ω nominal
 Speaker Bracket: N/A
 Warranty: IntraSonic 10 Year



JA-D6AII

Power Handling: 10~100 Watts
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 55 Hz - 22,000 Hz \pm 3 dB
 Color: White
 Overall Dimensions: 9 1/2" DIA x 3 1/8" DPT
 Install Dimensions: 8" DIA
 Cone Type and Size: Dual voice coil in-ceiling speaker, 6 1/2" Aluminum Cone with a Rubber Surround
 Crossover: 24 dB
 Tweeter: (2) 3/4" Aluminum Dome Swivel Tweeter with Ferrofluid Cooled Voice Coil
 Efficiency: 90 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-8C
 Warranty: IntraSonic 10 Year



I30W

Power Handling: 30
 Mounting: Cam-Lock
 Grille: White Metal
 Frequency: 48 Hz - 20 kHz
 Overall Dimensions: 8 3/4" W x 12" H x 2 1/2" DPT
 Install Dimensions: 7 3/8" W x 10 3/4" H
 Tweeter Type and Size: Mylar 1/2"
 Magnet Weight: 10 oz
 Cone Type and Size: 6 1/2" Coated Paper
 Db Sensitivity: 88 db
 Impedance: 8 Ω nominal
 Speaker Bracket: SPKBKT-61W
 Warranty: IntraSonic 10 Year



I100W

Power Handling: 100
 Mounting: Cam-Lock
 Grille: White Metal
 Frequency: 36 Hz - 22 kHz
 Overall Dimensions: 10" W x 14 1/4" H x 3 1/2" DPT
 Install Dimensions: 8 7/8" W x 12 7/8" H
 Tweeter Type and Size: 360° directional Laminated Alum PP1
 Magnet Weight: 13.3 oz
 Cone Type and Size: 8" Laminated PP
 Db Sensitivity: 89 db
 Impedance: 8 Ω nominal
 Bass and Treble: 3 Position Adjustable
 Speaker Bracket: SPKBKT-8IW
 Warranty: IntraSonic 10 Year



EX-180II

Power Handling: 45~150 Watts
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 45 Hz - 22,000 Hz \pm 3 dB
 Overall Dimensions: 14 3/8" W x 10 1/8" H x 3 3/4" DPT
 Install Dimensions: 12 3/4" W x 8 3/4" H
 Cone Type and Size: 8" Yellow Fiberglass Cone with a Rubber Surround
 Crossover: Hi-End 12 dB, Adjustable for Tweeter & Woofer Level \pm 3 dB
 Tweeter: 1" Titanium Swivel Dome Tweeter with Ferrofluid Cooled Voice Coil
 Efficiency: 88 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-8IW
 Warranty: IntraSonic 10 Year



EX-165II

Power Handling: 5~100 Watts
 Mounting: Cam-Lock
 Grille: White Aluminum
 Frequency: 50 Hz - 22,000 Hz \pm 3 dB
 Overall Dimensions: 12" W x 8 11/16" H x 3 11/16" DPT
 Install Dimensions: 7 1/4" W x 10 3/4" H
 Cone Type and Size: 6 1/2" yellow Fiberglass Cone with a Rubber Surround
 Crossover: Hi-End 18 dB, Adjustable for Tweeter & Woofer Level \pm dB
 Tweeter: 1" Titanium Dome Eyeball Swivel Tweeter with Cooled Voice Coil
 Efficiency: 90 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-6IW
 Warranty: IntraSonic 10 Year



JA-I8AII

Power Handling: 10~150
 Mounting: Cam-Lock
 Grille: White Metal
 Frequency: 42 Hz - 22,000 Hz
 Overall Dimensions: 10" W x 14 1/16" H x 3 1/4" DPT
 Install Dimensions: 8 3/4" W x 12 7/8" H
 Cone Type and Size: 8" Aluminum Cone Woofer with a Rubber Surround
 Crossover: 24 dB High - Low pass
 Tweeter: 1" Titanium Dome Swivel Ferrofluid Cooled Voice Coil
 Efficiency: 90 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-8IW
 Warranty: IntraSonic 10 Year



JA-I6AII

Power Handling: 10~100
 Mounting: Cam-Lock
 Grille: White Metal
 Frequency: 50 Hz - 22,000 Hz
 Overall Dimensions: 8 3/4" W x 12 1/16" H x 3 1/4" DPT
 Install Dimensions: 7 1/4" W x 10 11/16" H
 Cone Type and Size: 6 1/2" Aluminum Cone with a Rubber Surround
 Crossover: 24 dB High - Low pass
 Tweeter: 1" Aluminum Dome Swivel With Ferrofluid Cooled Voice
 Efficiency: 90 db
 Impedance: 8 Ω nominal, 6 Ω minimum
 Speaker Bracket: SPKBKT-6IW
 Warranty: IntraSonic 10 Year



B3-HTPACK

5.1 Mini-Cube Surround Sound
 Includes: (5) Each JA-B3 Mini Cubes
 (1) JA-SS10 Subwoofer
 (1) I51W Home Theater Wall Plate
 Colors: White or Black Mini-Cubes





JA-B3II

Power Handling: 100 (35 Watts Continuous)
 Mounting: Adjustable Swivel Bracket Included
 Frequency: 250 Hz – 18 kHz
 Color: White or Black
 Dimensions: 3 1/4" W X 7" H x 4 3/4" DPT
 Sensitivity: 91 dB/Wm
 Impedance: 6 Ω minimum
 Warranty: IntraSonic 10 Year

JA-T5

Power Handling: 20~120
 Mounting: Bracket
 Frequency: 50 Hz - 22,000 Hz
 Color: White
 Overall Dimensions: 7 1/16" W x 9 11/16" H x 6 9/17" DPT
 Cone Type and Size: 5 1/4" Polypropylene with a Rubber Surround
 Tweeter: 5/8" liquid-cooled polycarbonate
 Sensitivity: 89 dB 1W/1M
 Impedance: 8 Ω minimum
 Warranty: IntraSonic 2 Year



ROCK-RK820

Power Handling: 250
 Frequency: 100 Hz – 22 kHz 3 dB
 Color: Grey or Red
 Cone Type and Size: 8" Black Polypropylene Cone
 Tweeter: 2" Polypropylene
 Impedance: 8 Ω nominal, 6 Ω minimum
 Warranty: IntraSonic 2 Year



JA-SS7

Power Handling: 80 (120 Watts Max)
 Frequency: 55 Hz ~ 600 Hz
 Overall Dimensions: 9 7/8" W x 13" H x 14" DPT
 Cone Type and Size: 6" x 9" Long-Throw Woofer to Reproduce Low Frequency's
 Bass Booster: 20 Hz + 5 dB
 Frequency: 18 dB High – Low Pass
 Auto power input signal level: 5 mv
 Impedance: 8 Ω nominal
 Warranty: IntraSonic 2 Year

JA-SS10

Power Handling: 120 (200 Watts Max)
 Frequency: 50 Hz ~ 400 Hz
 Overall Dimensions: 14 1/2" W x 15 H X 14 1/2" DPT
 Cone Type and Size: 10" Long-Throw Woofer to Reproduce Low Frequency's
 Bass Booster: 20 Hz + 5 dB
 Frequency: 50 Hz ~ 400 Hz
 Auto power input signal level: 5 mv
 Impedance: 8 Ω nominal
 Warranty: IntraSonic 2 Year



JA-VNB-75

Power Handling: 75 RMS/150 Max
 Attenuation: 34-0 dB in 12 position
 Frequency: 35 Hz – 20 kHz
 Color: White
 Overall Dimensions: 14 1/8" x 10 1/8" x 4"
 Warranty: IntraSonic 2 Year



JA-VSL-100

Power Handling: 100 RMS/180 Max
 Attenuation: 34-0 dB in 12 position
 Frequency: 35 Hz – 20 kHz
 Color: White
 Warranty: IntraSonic 2 Year



For more details, larger images of products, and updates on new products, visit our website at



jaaudio.com

Intrasonic Technology, headquartered in Dallas, TX, manufactures full-featured, easy-to-use music distribution and intercom systems that offer great value for the price. Our diverse line of products includes Music Distribution and Intercom Systems, Video Door Intercom Systems, and a wide variety of ceiling, in-wall, or mini-cube audio speakers, and associated accessories. Product names and model numbers referenced or depicted on this brochure are trademarks or registered trademarks of Intrasonic Technology, Inc.

Learn more today! Contact your JA Audio representative shown below, or for more information, visit jaaudio.com.

