



The Doberman Plus

Indoor/Outdoor Siren & Strobe Combination
Sku: 4102147416



Features:

- Tamper switch on back of unit
- Strobe can be independently wired from siren
- Single tone piezo siren – warble
- Strobe flashes at same rate as siren sounding
- Mounts onto single gang box or can be surface mounted with two screws
- CE Approved

Specifications:

Operating voltage:	6 - 14 VDC
Sound output:	104 dB @ 12 VDC
Current draw:	140 mA @ 12 VDC; 40 mA at 12 VDC strobe only
Dimensions:	2.9" x 4.8" x 1.7"
Color:	Ivory body with clear lens & red strobe
Material:	UV-resistant, high impact polycarbonate plastic
Wiring:	Red-positive (strobe & siren); Brown-positive (strobe only); Black-common