



SGST-W

Single Gang/Single Tone Piezo Siren
Sku: 41111494316



Features:

- Single tone piezo siren - steady
- Polarized for DC supervision
- Mounts into a single gang box

Specifications:

Operating voltage:	9.6 - 30 VDC
Sound output:	105 dB @ 24 VDC
Current draw:	20 mA @ 24 VDC
Frequency:	3.4 KHz +/- 0.5
Dimensions:	4.6
Colors:	White
Materials:	Fire-resistant ABS plastic
Wiring:	+ for positive wire, - for common wire