

PROXIMITY CARDREADERS ACCESS CONTROL

• CONDOMINIUM/RESIDENTS HALLS • GATED COMMUNITIES • COMMERCIAL/INDUSTRIAL • MIXED USE • PARKING • SELF STORAGE • MAXIMUM SECURITY



- Full line proximity card readers and cards
- Mullion, wall and post mount models
- Read ranges from 2-inches up to 30-inches (50.8mm to 76.2cm)
- 5 year limited factory warranty



indoor use



outdoor use




post mount



cards & tags

ACCESS CONTROL SOLUTIONS

PROXIMITY CARD READERS ACCESS CONTROL



1815-300

Mullion

1815-301

Single Gang

1815-301

2.88" W x 4.44" H

73.2mm W x 112.7mm H


4-inch read range (101.6mm)



1815-302 Small

1815-302

1.69" W x 3.13" H 42.9mm W x 79.5mm H 2-inch read range (50.8mm)




1815-305

1815-305

9.38" W x 9.38" H x 1.38" D 238.3mm W x 238.3mm H x 35mm D 30-inch read range (762mm)

1815-300

1.81" W x 4.44" H 46mm W x 112.7mm H 3-inch read range (76.2mm)



Technical Features

Cards

DK Cards / Key Tags

These cards will work with the following DK Prox readers only: 1815-300, 1815-301, 1815-302, 1815-330, 1815-331, 1815-305. Cards are sold in blocks of 50 only.

Cards

These cards are factory pre-coded. Card numbers may, or may not be, in numerical sequence.

1508-120 Clamshell Cards

1508-121 ISO Graphics Cards

1508-123 Key Tags

Special Order

These cards include sequential coding, specific card numbers and specific start / stop numbering sequences

1508-127 Clamshell Cards

1508-128 ISO Graphics Cards

1508-129 Key Tags

 $MicroPlus^{\circledast}$ and $MicroClik^{\circledast}$ $ProxMitters^{{}^{\rm TM}}$ (Card + Transmitter) are available

Readers

26-bit weigand output Most readers operate on 5-12 VDC Proximity readers are not designed for stand-alone operation and must be connected to an access controller

DKS Readers

1815-300; up to 3-inch read range 1815-301; up to 4-inch read range 1815-302; up to 2-inch read range

1815-305; up to 30-inch read range

1815-330; 1815-300 reader on a surface mount enclosure 1815-333; same as 1815-330 but also includes a Tracker

expansion board

1504-124; 1815-300 mounted on surface enclosure with built in intercom substation $\label{eq:substation}$

Optional

Surface / Gooseneck mount enclosure for the DKS 1815-305 Include Tracker Board with the mount enclosure 1815-231

Electrical

Input voltage / current	
1815-300:	12 VDC – 200mA
1815-301:	12 VDC – 200mA
1815-302:	12 VDC - 200 mA
1815-305:	12 VDC Regulated - 2.0 A

2 color LED (Red, Green), Piezo Beeper Frequency: 125 kHz Output Format 26-bit wiegand

Operating Environment: -31°F to 149°F (-35°C to 65°C)



Rev. 2/15

Distributed by:



Access Control Solutions since 1948

MEMBER:







DOORKING, INC. 120 Glasgow Avenue, Inglewood, California 90301 U.S.A. Tel: 310-645-0023 FAX: 310-641-1586 www.doorking.com © 2015 All Rights Reserved. Product specifications may change without notice.